

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278666

Luminaire Tested: **LDA2B109035D010 EU2B10NFL259035 2LBALD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109035D010 EU2B10NFL259035 2LBALD1LI
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 885.1 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278666

CATALOG NUMBER: LDA2B109035D010 EU2B10NFL259035 2LBALD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P278666

CATALOG NUMBER: LDA2B109035D010 EU2B10NFL259035 2LBALD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																											
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97																											
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94																											
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91																											
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89																											
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86																											
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84																											
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82																											
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80																											
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78																											
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76									76																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2265567
5°	2089395
10°	1407984
15°	694182
20°	296534
25°	116548
30°	45917
35°	20116
40°	9661
45°	4675
50°	2533
55°	1462
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P278666

CATALOG NUMBER: LDA2B109035D010 EU2B10NFL259035 2LBALD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	357.4	40.4
10°-20°	384.9	43.5
20°-30°	111.1	12.6
30°-40°	23.5	2.6
40°-50°	5.8	0.7
50°-60°	1.7	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	853.4	96.4
0°-40°	876.8	99.1
0°-60°	884.3	99.9
0°-90°	885.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	885.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4592	
5°	4219	357
15°	1359	385
25°	214	111
35°	33	23
45°	7	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278666

CATALOG NUMBER: LDA2B109035D010 EU2B10NFL259035 2LBALD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4592.1
1°	4563.3
2°	4514.4
3°	4448.5
4°	4355.0
5°	4218.9
6°	4035.2
7°	3795.6
8°	3500.9
9°	3157.4
10°	2810.5
11°	2459.9
12°	2128.9
13°	1835.0
14°	1576.6
15°	1359.1
17.5°	898.3
20°	564.8
22.5°	347.3
25°	214.1
27.5°	130.7
30°	80.6
32.5°	50.9
35°	33.4
37.5°	22.1
40°	15.0
42.5°	10.4
45°	6.7
47.5°	4.2
50°	3.3
52.5°	2.5
55°	1.7
57.5°	1.3
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P278666

CATALOG NUMBER: LDA2B109035D010 EU2B10NFL259035 2LBALD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)