

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498194

Luminaire Tested: **LDA2B158050R60D010 2LBD1MW**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P498194  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B158050R60D010 2LBD1MW  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1450.6 lumens  
Efficiency: N/A  
Efficacy: 102.9 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P498194

CATALOG NUMBER: LDA2B158050R60D010 2LBD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P498194

CATALOG NUMBER: LDA2B158050R60D010 2LBD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	868465
5°	824437
10°	807117
15°	781216
20°	714244
25°	634130
30°	474377
35°	267835
40°	100856
45°	45142
50°	22028
55°	4387
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P498194

CATALOG NUMBER: LDA2B158050R60D010 2LBD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.6	10.9
10°-20°	424.8	29.3
20°-30°	519.0	35.8
30°-40°	283.1	19.5
40°-50°	56.7	3.9
50°-60°	8.1	0.6
60°-70°	1.0	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1101.4	75.9
0°-40°	1384.5	95.4
0°-60°	1449.3	99.9
0°-90°	1450.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1450.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1760	
5°	1665	158
15°	1530	425
25°	1165	519
35°	445	283
45°	65	57
55°	5	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498194

CATALOG NUMBER: LDA2B158050R60D010 2LBD1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1760.3
1°	1752.2
2°	1736.8
3°	1716.2
4°	1686.8
5°	1664.7
6°	1653.0
7°	1639.0
8°	1628.0
9°	1622.8
10°	1611.1
11°	1597.8
12°	1586.1
13°	1572.1
14°	1551.5
15°	1529.5
16°	1501.6
17°	1462.6
18°	1437.6
19°	1397.2
20°	1360.4
21°	1326.6
22.5°	1270.0
23°	1246.5
24°	1210.5
25°	1164.9
26°	1106.9
27°	1045.9
28°	976.1
29°	909.9
30°	832.7
32.5°	638.7
35°	444.7
37.5°	278.6
40°	156.6
42.5°	97.8
45°	64.7
47.5°	44.1
50°	28.7
52.5°	14.7
55°	5.1
57.5°	2.2
60°	1.5
62.5°	1.5
65°	0.7



TEST NUMBER: P498194

CATALOG NUMBER: LDA2B158050R60D010 2LBD1MW

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)