

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496697

Luminaire Tested: **LDA2B109050R60D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496697
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109050R60D010 2LBDLC1MMS
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 916.0 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496697

CATALOG NUMBER: LDA2B109050R60D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P496697

CATALOG NUMBER: LDA2B109050R60D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	542155
5°	528032
10°	513497
15°	488037
20°	445956
25°	382906
30°	284956
35°	167254
40°	79732
45°	37188
50°	18574
55°	6451
60°	1480
65°	1167
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P496697

CATALOG NUMBER: LDA2B109050R60D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	11.0
10°-20°	265.9	29.0
20°-30°	315.7	34.5
30°-40°	178.2	19.5
40°-50°	46.3	5.1
50°-60°	8.4	0.9
60°-70°	0.9	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	681.9	74.4
0°-40°	860.1	93.9
0°-60°	914.8	99.9
0°-90°	916.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	916.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1099	
5°	1066	100
15°	956	266
25°	703	316
35°	278	178
45°	53	46
55°	8	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496697

CATALOG NUMBER: LDA2B109050R60D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1098.9
1°	1099.4
2°	1091.9
3°	1085.3
4°	1072.8
5°	1066.2
6°	1054.6
7°	1046.1
8°	1038.0
9°	1032.5
10°	1025.0
11°	1010.4
12°	996.8
13°	989.2
14°	971.6
15°	955.5
16°	936.9
17°	914.8
18°	893.6
19°	868.5
20°	849.4
21°	823.2
22.5°	779.9
23°	772.4
24°	735.6
25°	703.4
26°	667.7
27°	626.4
28°	585.7
29°	545.9
30°	500.2
32.5°	384.9
35°	277.7
37.5°	189.7
40°	123.8
42.5°	81.0
45°	53.3
47.5°	36.2
50°	24.2
52.5°	15.1
55°	7.5
57.5°	3.0
60°	1.5
62.5°	1.0
65°	1.0



TEST NUMBER: P496697

CATALOG NUMBER: LDA2B109050R60D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)