

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315008

Luminaire Tested: **LDA2B10NFL9035D010 PINW1MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P315008  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B10NFL9035D010 PINW1MB  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in Adj PinHole, White oculus black finish  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 830.9 lumens  
Efficiency: N/A  
Efficacy: 83.1 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P315008

CATALOG NUMBER: LDA2B10NFL9035D010 PINW1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P315008

CATALOG NUMBER: LDA2B10NFL9035D010 PINW1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97																			
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94																			
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91																			
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89																			
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86																			
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84																			
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82																			
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80																			
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78																			
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76									76																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2126636
5°	1961275
10°	1321666
15°	651635
20°	278316
25°	109417
30°	43068
35°	18851
40°	9081
45°	4396
50°	2379
55°	1376
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P315008

CATALOG NUMBER: LDA2B10NFL9035D010 PINW1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	335.5	40.4
10°-20°	361.3	43.5
20°-30°	104.3	12.6
30°-40°	22.0	2.6
40°-50°	5.4	0.7
50°-60°	1.6	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	801.0	96.4
0°-40°	823.1	99.1
0°-60°	830.1	99.9
0°-90°	830.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	830.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4310	
5°	3960	335
15°	1276	361
25°	201	104
35°	31	22
45°	6	5
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315008

CATALOG NUMBER: LDA2B10NFL9035D010 PINW1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4310.5
1°	4283.5
2°	4237.6
3°	4175.7
4°	4088.0
5°	3960.2
6°	3787.8
7°	3562.9
8°	3286.3
9°	2963.8
10°	2638.2
11°	2309.1
12°	1998.3
13°	1722.5
14°	1479.9
15°	1275.8
17.5°	843.2
20°	530.1
22.5°	326.0
25°	201.0
27.5°	122.6
30°	75.6
32.5°	47.8
35°	31.3
37.5°	20.8
40°	14.1
42.5°	9.8
45°	6.3
47.5°	3.9
50°	3.1
52.5°	2.4
55°	1.6
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P315008

CATALOG NUMBER: LDA2B10NFL9035D010 PINW1MB

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)