

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278844

Luminaire Tested: **LDA2B159024D010 EU2B15NFL259024 2LBALD1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278844  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B159024D010 EU2B15NFL259024 2LBALD1MW  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl w/lens Self-Flanged, MW  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1009.2 lumens  
Efficiency: N/A  
Efficacy: 71.6 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278844

CATALOG NUMBER: LDA2B159024D010 EU2B15NFL259024 2LBALD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P278844

CATALOG NUMBER: LDA2B159024D010 EU2B15NFL259024 2LBALD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97													97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94													94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91													91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89													89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86													86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84													84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82													82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80													80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78													78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76													76															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2583045
5°	2382184
10°	1605317
15°	791483
20°	338063
25°	132879
30°	52354
35°	22947
40°	11013
45°	5303
50°	2917
55°	1634
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P278844

CATALOG NUMBER: LDA2B159024D010 EU2B15NFL259024 2LBALD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	407.5	40.4
10°-20°	438.8	43.5
20°-30°	126.7	12.6
30°-40°	26.8	2.7
40°-50°	6.6	0.7
50°-60°	1.9	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	973.0	96.4
0°-40°	999.7	99.1
0°-60°	1008.2	99.9
0°-90°	1009.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5236	
5°	4810	407
15°	1550	439
25°	244	127
35°	38	27
45°	8	7
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278844

CATALOG NUMBER: LDA2B159024D010 EU2B15NFL259024 2LBALD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5235.6
1°	5202.8
2°	5147.1
3°	5071.9
4°	4965.3
5°	4810.1
6°	4600.7
7°	4327.6
8°	3991.6
9°	3599.9
10°	3204.4
11°	2804.6
12°	2427.2
13°	2092.2
14°	1797.6
15°	1549.6
17.5°	1024.2
20°	643.9
22.5°	396.0
25°	244.1
27.5°	149.0
30°	91.9
32.5°	58.1
35°	38.1
37.5°	25.2
40°	17.1
42.5°	11.9
45°	7.6
47.5°	4.8
50°	3.8
52.5°	2.9
55°	1.9
57.5°	1.4
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P278844

CATALOG NUMBER: LDA2B159024D010 EU2B15NFL259024 2LBALD1MW

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)