

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278122

Luminaire Tested: **LDA2B159024D010 EU2B15SP159024 2LBAD1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278122  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B159024D010 EU2B15SP159024 2LBAD1H  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, H  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1032.9 lumens  
Efficiency: N/A  
Efficacy: 73.3 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278122

CATALOG NUMBER: LDA2B159024D010 EU2B15SP159024 2LBAD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P278122

CATALOG NUMBER: LDA2B159024D010 EU2B15SP159024 2LBAD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98			
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96			
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93			
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92			
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90			
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88			
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86			
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85			
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83			
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4666462
5°	3720390
10°	1615186
15°	558063
20°	228806
25°	103320
30°	41587
35°	19333
40°	10498
45°	3907
50°	2379
55°	1720
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P278122

CATALOG NUMBER: LDA2B159024D010 EU2B15SP159024 2LBAD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	567.7	55.0
10°-20°	341.0	33.0
20°-30°	93.9	9.1
30°-40°	22.3	2.2
40°-50°	5.5	0.5
50°-60°	1.8	0.2
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1002.6	97.1
0°-40°	1024.9	99.2
0°-60°	1032.2	99.9
0°-90°	1032.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1032.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9458	
5°	7512	568
15°	1093	341
25°	190	94
35°	32	22
45°	6	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278122

CATALOG NUMBER: LDA2B159024D010 EU2B15SP159024 2LBAD1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9458.5
1°	9353.9
2°	9103.3
3°	8721.1
4°	8181.7
5°	7512.2
6°	6694.7
7°	5799.1
8°	4858.1
9°	3992.6
10°	3224.1
11°	2573.5
12°	2048.4
13°	1651.9
14°	1336.5
15°	1092.6
17.5°	678.2
20°	435.8
22.5°	285.8
25°	189.8
27.5°	122.0
30°	73.0
32.5°	45.9
35°	32.1
37.5°	23.5
40°	16.3
42.5°	9.7
45°	5.6
47.5°	4.1
50°	3.1
52.5°	2.6
55°	2.0
57.5°	1.5
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P278122

CATALOG NUMBER: LDA2B159024D010 EU2B15SP159024 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)