

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496859

Luminaire Tested: **LDA2B109727R35D010 2LBDL1WH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496859
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-29)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109727R35D010 2LBDL1WH
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 702.3 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.51
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496859

CATALOG NUMBER: LDA2B109727R35D010 2LBDL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P496859

CATALOG NUMBER: LDA2B109727R35D010 2LBDL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	87	85
5	100	93	89	86	98	93	88	85	91	87	85	89	86	84	88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79
7	93	86	82	79	92	86	82	79	85	81	78	84	80	78	83	80	77	76
8	90	83	79	76	89	83	79	76	82	78	75	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	72	71
10	85	78	74	71	84	78	73	71	77	73	70	76	73	70	76	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1071927
5°	1036303
10°	905608
15°	633145
20°	332446
25°	142841
30°	65343
35°	31680
40°	16101
45°	8233
50°	4528
55°	1892
60°	691
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P496859

CATALOG NUMBER: LDA2B109727R35D010 2LBDL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.8	27.2
10°-20°	330.8	47.1
20°-30°	132.0	18.8
30°-40°	36.0	5.1
40°-50°	10.0	1.4
50°-60°	2.3	0.3
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	653.5	93.1
0°-40°	689.6	98.2
0°-60°	701.9	99.9
0°-90°	702.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	702.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2173	
5°	2092	191
15°	1240	331
25°	262	132
35°	53	36
45°	12	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496859

CATALOG NUMBER: LDA2B109727R35D010 2LBDL1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2172.7
1°	2163.5
2°	2154.7
3°	2141.4
4°	2121.6
5°	2092.5
6°	2054.7
7°	2007.7
8°	1954.0
9°	1879.8
10°	1807.7
11°	1718.4
12°	1604.1
13°	1489.1
14°	1371.9
15°	1239.6
16°	1109.5
17°	975.7
18°	855.5
19°	742.0
20°	633.2
21°	533.2
22.5°	413.4
23°	374.9
24°	314.6
25°	262.4
26°	220.9
27°	184.5
28°	156.2
29°	133.0
30°	114.7
32.5°	76.8
35°	52.6
37.5°	36.8
40°	25.0
42.5°	16.9
45°	11.8
47.5°	8.5
50°	5.9
52.5°	4.0
55°	2.2
57.5°	1.1
60°	0.7
62.5°	0.7
65°	0.4



TEST NUMBER: P496859

CATALOG NUMBER: LDA2B109727R35D010 2LBDL1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)