

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498462

Luminaire Tested: **LDA2B159024R70D010 2LBDL1H**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498462
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159024R70D010 2LBDL1H
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 915.7 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498462
CATALOG NUMBER: LDA2B159024R70D010 2LBDL1H

Luminous Intensity Polar Plot





TEST NUMBER: P498462

CATALOG NUMBER: LDA2B159024R70D010 2LBDL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	362572
5°	360440
10°	358045
15°	351407
20°	338693
25°	324278
30°	308883
35°	254886
40°	165647
45°	86587
50°	40296
55°	14709
60°	1480
65°	1167
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P498462

CATALOG NUMBER: LDA2B159024R70D010 2LBDL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	7.5
10°-20°	193.3	21.1
20°-30°	274.4	30.0
30°-40°	256.6	28.0
40°-50°	103.2	11.3
50°-60°	18.0	2.0
60°-70°	0.9	0.1
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.6	58.6
0°-40°	793.2	86.6
0°-60°	914.4	99.9
0°-90°	915.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	915.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	735	
5°	728	69
15°	688	193
25°	596	274
35°	423	257
45°	124	103
55°	17	18
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498462

CATALOG NUMBER: LDA2B159024R70D010 2LBDL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	734.9
1°	735.9
2°	734.4
3°	731.3
4°	729.8
5°	727.8
6°	719.7
7°	722.3
8°	715.2
9°	713.7
10°	714.7
11°	708.1
12°	706.6
13°	698.6
14°	695.5
15°	688.0
16°	683.4
17°	674.4
18°	663.8
19°	657.7
20°	645.1
21°	635.5
22.5°	617.9
23°	613.3
24°	604.7
25°	595.7
26°	588.6
27°	578.5
28°	568.4
29°	556.3
30°	542.2
32.5°	492.8
35°	423.2
37.5°	341.0
40°	257.2
42.5°	183.6
45°	124.1
47.5°	81.7
50°	52.5
52.5°	32.8
55°	17.1
57.5°	5.5
60°	1.5
62.5°	1.0
65°	1.0



TEST NUMBER: P498462

CATALOG NUMBER: LDA2B159024R70D010 2LBDL1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)