

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496940

Luminaire Tested: **LDA2B109727R70D010 2LBD1H**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496940  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109727R70D010 2LBD1H  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 720.6 lumens  
Efficiency: N/A  
Efficacy: 72.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496940  
CATALOG NUMBER: LDA2B109727R70D010 2LBD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P496940

CATALOG NUMBER: LDA2B109727R70D010 2LBD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50		59	54	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	281562
5°	278477
10°	277088
15°	276120
20°	266240
25°	255253
30°	252712
35°	215798
40°	134668
45°	62306
50°	22566
55°	1548
60°	691
65°	817
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P496940

CATALOG NUMBER: LDA2B109727R70D010 2LBD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.3	7.4
10°-20°	151.4	21.0
20°-30°	217.7	30.2
30°-40°	214.6	29.8
40°-50°	76.5	10.6
50°-60°	6.3	0.9
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.4	58.6
0°-40°	637.0	88.4
0°-60°	719.8	99.9
0°-90°	720.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	720.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	571	
5°	562	53
15°	541	151
25°	469	218
35°	358	215
45°	89	76
55°	2	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496940

CATALOG NUMBER: LDA2B109727R70D010 2LBD1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	570.7
1°	570.7
2°	569.6
3°	570.0
4°	565.2
5°	562.3
6°	558.2
7°	556.8
8°	554.9
9°	554.6
10°	553.1
11°	551.2
12°	551.2
13°	547.9
14°	543.5
15°	540.6
16°	534.7
17°	531.4
18°	521.1
19°	514.1
20°	507.1
21°	498.0
22.5°	485.1
23°	480.0
24°	475.2
25°	468.9
26°	465.3
27°	459.0
28°	458.3
29°	451.7
30°	443.6
32.5°	412.3
35°	358.3
37.5°	288.1
40°	209.1
42.5°	143.0
45°	89.3
47.5°	53.3
50°	29.4
52.5°	11.0
55°	1.8
57.5°	1.1
60°	0.7
62.5°	0.7
65°	0.7



TEST NUMBER: P496940

CATALOG NUMBER: LDA2B109727R70D010 2LBD1H

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)