

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498468

Luminaire Tested: **LDA2B159024R70D010 2LBDL1WHH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P498468  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159024R70D010 2LBDL1WHH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 915.7 lumens  
Efficiency: N/A  
Efficacy: 64.9 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P498468

CATALOG NUMBER: LDA2B159024R70D010 2LBDL1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P498468

CATALOG NUMBER: LDA2B159024R70D010 2LBDL1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	362572
5°	360440
10°	358045
15°	351407
20°	338693
25°	324278
30°	308883
35°	254886
40°	165647
45°	86587
50°	40296
55°	14709
60°	1480
65°	1167
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P498468

CATALOG NUMBER: LDA2B159024R70D010 2LBDL1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.8	7.5
10°-20°	193.3	21.1
20°-30°	274.4	30.0
30°-40°	256.6	28.0
40°-50°	103.2	11.3
50°-60°	18.0	2.0
60°-70°	0.9	0.1
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.6	58.6
0°-40°	793.2	86.6
0°-60°	914.4	99.9
0°-90°	915.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	915.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	735	
5°	728	69
15°	688	193
25°	596	274
35°	423	257
45°	124	103
55°	17	18
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498468

CATALOG NUMBER: LDA2B159024R70D010 2LBDL1WHH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	734.9
1°	735.9
2°	734.4
3°	731.3
4°	729.8
5°	727.8
6°	719.7
7°	722.3
8°	715.2
9°	713.7
10°	714.7
11°	708.1
12°	706.6
13°	698.6
14°	695.5
15°	688.0
16°	683.4
17°	674.4
18°	663.8
19°	657.7
20°	645.1
21°	635.5
22.5°	617.9
23°	613.3
24°	604.7
25°	595.7
26°	588.6
27°	578.5
28°	568.4
29°	556.3
30°	542.2
32.5°	492.8
35°	423.2
37.5°	341.0
40°	257.2
42.5°	183.6
45°	124.1
47.5°	81.7
50°	52.5
52.5°	32.8
55°	17.1
57.5°	5.5
60°	1.5
62.5°	1.0
65°	1.0



TEST NUMBER: P498468

CATALOG NUMBER: LDA2B159024R70D010 2LBDL1WHH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)