

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315074

Luminaire Tested: **LDA2B15NFL9024D010 PINW1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B15NFL9024D010 PINW1MB
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in Adj PinHole, White oculus black finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 947.2 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315074

CATALOG NUMBER: LDA2B15NFL9024D010 PINW1MB

Luminous Intensity Polar Plot





TEST NUMBER: P315074

CATALOG NUMBER: LDA2B15NFL9024D010 PINW1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2424676
5°	2236136
10°	1506876
15°	742960
20°	317325
25°	124768
30°	49107
35°	21502
40°	10369
45°	4954
50°	2763
55°	1548
60°	888
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P315074

CATALOG NUMBER: LDA2B15NFL9024D010 PINW1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	382.5	40.4
10°-20°	411.9	43.5
20°-30°	118.9	12.6
30°-40°	25.1	2.7
40°-50°	6.2	0.7
50°-60°	1.8	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	913.3	96.4
0°-40°	938.4	99.1
0°-60°	946.4	99.9
0°-90°	947.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	947.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4915	
5°	4515	382
15°	1455	412
25°	229	119
35°	36	25
45°	7	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315074

CATALOG NUMBER: LDA2B15NFL9024D010 PINW1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	4914.6
1°	4883.8
2°	4831.5
3°	4760.9
4°	4660.8
5°	4515.2
6°	4318.6
7°	4062.2
8°	3746.8
9°	3379.1
10°	3007.9
11°	2632.6
12°	2278.4
13°	1963.9
14°	1687.3
15°	1454.6
17.5°	961.4
20°	604.4
22.5°	371.7
25°	229.2
27.5°	139.8
30°	86.2
32.5°	54.5
35°	35.7
37.5°	23.7
40°	16.1
42.5°	11.2
45°	7.1
47.5°	4.5
50°	3.6
52.5°	2.7
55°	1.8
57.5°	1.3
60°	0.9
62.5°	0.9
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P315074

CATALOG NUMBER: LDA2B15NFL9024D010 PINW1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)