

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498485

Luminaire Tested: **LDA2B159027R20D010 2LBD1MW-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498485
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159027R20D010 2LBD1MW-30DEG TILT
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 708.8 lumens
Efficiency: N/A
Efficacy: 50.3 lumens/watt
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498485

CATALOG NUMBER: LDA2B159027R20D010 2LBD1MW-30DEG TILT

Luminous Intensity Polar Plot



0% Up
100% Dn

— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P498485

CATALOG NUMBER: LDA2B159027R20D010 2LBD1MW-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82					82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74					74			
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66					66			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43					43			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38					38			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	11249	11249	11249
5°	21543	9954	7280
10°	51450	8717	4910
15°	299768	6946	1941
20°	1495428	4305	578
25°	2726776	1470	0
30°	3198155	0	0
35°	2799233	0	0
40°	2067169	0	0
45°	745094	0	0
50°	155196	0	0
55°	35524	430	0
60°	11249	493	0
65°	2568	1284	0
70°	0	1587	721
75°	0	2097	0
80°	0	3125	0
85°	0	6227	0



TEST NUMBER: P498485

CATALOG NUMBER: LDA2B159027R20D010 2LBD1MW-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.6	0.4
10°-20°	39.0	5.5
20°-30°	262.5	37.0
30°-40°	306.7	43.3
40°-50°	89.4	12.6
50°-60°	6.0	0.8
60°-70°	1.1	0.2
70°-80°	0.9	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	304.0	42.9
0°-40°	610.7	86.2
0°-60°	706.1	99.6
0°-90°	708.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	708.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	23	23	23	23	23	
5°	44	32	20	17	15	6
15°	587	66	14	7	4	306
25°	5009	103	3	0	0	2218
35°	4648	55	0	0	0	2855
45°	1068	11	0	0	0	984
55°	41	2	0	0	0	53
65°	2	1	1	1	0	3
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P498485

CATALOG NUMBER: LDA2B159027R20D010 2LBD1MW-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	22.8	22.8	22.8	22.8	22.8	22.8	22.8	22.8	22.8
2.5°	29.3	29.3	26.1	23.4	21.2	20.1	19.6	18.5	17.9
5°	43.5	38.0	31.5	24.5	20.1	18.5	16.8	15.2	14.7
7.5°	63.6	55.4	38.0	25.0	19.0	16.3	14.7	13.0	12.0
10°	102.7	79.9	46.7	25.0	17.4	14.1	12.0	10.3	9.8
12.5°	189.7	122.3	56.0	24.5	15.8	12.0	9.2	8.2	6.5
15°	586.9	253.3	66.3	23.4	13.6	9.2	7.1	4.3	3.8
17.5°	1517.9	591.3	73.9	20.7	10.9	6.5	3.3	2.7	2.7
20°	2848.3	1072.2	84.8	17.9	8.2	4.3	2.2	1.6	1.1
21°	3249.3	1311.9	90.2	16.8	7.1	2.7	1.6	0.5	0.5
22°	3872.7	1573.3	94.6	15.8	6.0	1.6	1.1	0.5	0.0
23°	4316.7	1740.2	98.9	14.1	4.3	1.6	0.5	0.0	0.0
24°	4760.7	1952.7	101.6	13.0	3.8	1.1	0.5	0.0	0.0
25°	5009.1	2129.8	102.7	12.0	2.7	0.5	0.0	0.0	0.0
26°	5213.4	2248.3	103.3	10.9	1.6	0.0	0.0	0.0	0.0
27°	5388.4	2385.8	102.2	9.8	1.6	0.0	0.0	0.0	0.0
28°	5487.9	2408.6	100.5	8.7	0.5	0.0	0.0	0.0	0.0
29°	5530.8	2380.9	95.6	7.6	0.5	0.0	0.0	0.0	0.0
30°	5613.9	2354.8	90.8	7.1	0.0	0.0	0.0	0.0	0.0
31°	5537.3	2268.4	84.8	6.0	0.0	0.0	0.0	0.0	0.0
32°	5237.3	2195.6	77.7	4.9	0.0	0.0	0.0	0.0	0.0
33°	5147.7	2046.1	70.1	4.3	0.0	0.0	0.0	0.0	0.0
34°	4978.6	1823.9	63.6	3.8	0.0	0.0	0.0	0.0	0.0
35°	4647.7	1640.2	55.4	3.3	0.0	0.0	0.0	0.0	0.0
36°	4416.7	1430.4	48.4	2.7	0.0	0.0	0.0	0.0	0.0
37°	4174.9	1247.2	42.9	2.2	0.0	0.0	0.0	0.0	0.0
38°	3874.3	1054.9	36.4	1.6	0.0	0.0	0.0	0.0	0.0
39°	3524.3	871.7	31.0	1.6	0.0	0.0	0.0	0.0	0.0
40°	3209.7	702.7	26.6	1.1	0.0	0.0	0.0	0.0	0.0
42.5°	1980.9	401.1	15.8	1.1	0.0	0.0	0.0	0.0	0.0
45°	1067.9	243.5	11.4	0.5	0.0	0.0	0.0	0.0	0.0
47.5°	491.8	113.6	8.2	0.5	0.0	0.0	0.0	0.0	0.0
50°	202.2	50.5	6.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	72.8	28.3	3.8	0.0	0.0	0.5	0.0	0.0	0.0
55°	41.3	16.3	2.2	0.5	0.5	0.5	0.5	0.0	0.0
57.5°	19.6	9.2	0.5	0.5	0.5	0.5	0.5	0.0	0.0
60°	11.4	4.9	0.5	0.5	0.5	1.1	0.5	0.0	0.0
62.5°	5.4	1.6	0.5	1.1	1.1	1.1	1.1	0.5	0.0
65°	2.2	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.0
67.5°	0.5	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.5
70°	0.0	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.5
72.5°	0.0	0.5	1.1	1.1	1.1	1.6	1.1	0.5	0.5
75°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
77.5°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
80°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0



TEST NUMBER: P498485

CATALOG NUMBER: LDA2B159027R20D010 2LBD1MW-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
85°	0.0	0.5	1.1	1.1	1.1	1.1	1.1	0.5	0.0
87.5°	0.0	0.5	1.1	1.1	1.1	1.1	0.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)