

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498529

Luminaire Tested: **LDA2B159027R30D010 2LBD1WH**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498529
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-14)
Test Lab: INNOVATION CENTER
Issue Date: 3/12/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159027R30D010 2LBD1WH
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1037.2 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498529

CATALOG NUMBER: LDA2B159027R30D010 2LBD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P498529

CATALOG NUMBER: LDA2B159027R30D010 2LBD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20																				
RC	80					70					50					30					10					0															
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10			
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	102	102	102	100	100	102	102	102	100	100	102	102	102	100	100	102	102	102			
	1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77	
	2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	95	93	92	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70
	3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	92	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67	
	4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67	66	65	
	5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67	66	65	64	63	62	61	
	6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67	66	65	64	63	62	61	60	59	
	7	96	89	85	82	95	89	85	82	87	84	81	86	83	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67	66	65	64	63	62	61	60	59	58	57	56	
	8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	78	77	76	75	74	73	72	71	70	69	68	67	66	65	64	63	62	61	60	59	58	57	56	55	54	
	9	90	84	80	77	90	83	80	77	83	79	77	82	79	76	75	74	73	72	71	70	69	68	67	66	65	64	63	62	61	60	59	58	57	56	55	54	53	52	51	
	10	88	81	77	75	87	81	77	75	80	77	75	80	77	74	73	72	71	70	69	68	67	66	65	64	63	62	61	60	59	58	57	56	55	54	53	52	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2010104
5°	1916603
10°	1554318
15°	950177
20°	415137
25°	155307
30°	64374
35°	30114
40°	13976
45°	6838
50°	3761
55°	1376
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P498529

CATALOG NUMBER: LDA2B159027R30D010 2LBD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.2	33.3
10°-20°	498.4	48.1
20°-30°	148.8	14.3
30°-40°	34.2	3.3
40°-50°	8.4	0.8
50°-60°	1.9	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	992.4	95.7
0°-40°	1026.6	99.0
0°-60°	1036.9	100.0
0°-90°	1037.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1037.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4074	
5°	3870	345
15°	1860	498
25°	285	149
35°	50	34
45°	10	8
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498529

CATALOG NUMBER: LDA2B159027R30D010 2LBD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4074.3
1°	4065.1
2°	4023.8
3°	3996.1
4°	3944.4
5°	3870.0
6°	3768.4
7°	3647.2
8°	3492.8
9°	3304.8
10°	3102.6
11°	2886.3
12°	2640.7
13°	2376.6
14°	2125.5
15°	1860.3
16°	1603.8
17°	1351.0
18°	1147.2
19°	949.4
20°	790.7
21°	640.7
22.5°	475.0
23°	428.2
24°	350.5
25°	285.3
26°	234.2
27°	195.1
28°	160.9
29°	134.8
30°	113.0
32.5°	73.9
35°	50.0
37.5°	33.2
40°	21.7
42.5°	14.1
45°	9.8
47.5°	7.1
50°	4.9
52.5°	3.3
55°	1.6
57.5°	1.1
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P498529

CATALOG NUMBER: LDA2B159027R30D010 2LBD1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)