

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498542

Luminaire Tested: **LDA2B159027R30D010 2LBDL1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498542
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159027R30D010 2LBDL1MB
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1037.2 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498542
CATALOG NUMBER: LDA2B159027R30D010 2LBDL1MB

Luminous Intensity Polar Plot





TEST NUMBER: P498542

CATALOG NUMBER: LDA2B159027R30D010 2LBDL1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|---|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | | |
| 1 | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 97 | 96 | 95 | 95 | 95 | 97 | | |
| 2 | 111 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99 | 100 | 98 | 97 | 97 | 96 | 95 | 93 | 93 | 92 | 92 | 92 | 92 | 93 | | |
| 3 | 108 | 103 | 100 | 97 | 106 | 102 | 99 | 96 | 99 | 97 | 94 | 97 | 95 | 93 | 95 | 93 | 92 | 90 | 90 | 89 | 89 | 89 | 89 | 90 | | |
| 4 | 104 | 99 | 95 | 92 | 103 | 98 | 94 | 92 | 96 | 93 | 91 | 94 | 92 | 90 | 92 | 90 | 89 | 87 | 87 | 87 | 87 | 87 | 87 | 87 | | |
| 5 | 101 | 95 | 91 | 88 | 100 | 95 | 91 | 88 | 93 | 90 | 87 | 91 | 89 | 86 | 90 | 88 | 86 | 85 | 85 | 85 | 85 | 85 | 85 | 85 | | |
| 6 | 98 | 92 | 88 | 85 | 97 | 91 | 88 | 85 | 90 | 87 | 84 | 89 | 86 | 84 | 88 | 85 | 83 | 82 | 82 | 82 | 82 | 82 | 82 | 82 | | |
| 7 | 96 | 89 | 85 | 82 | 95 | 89 | 85 | 82 | 87 | 84 | 81 | 86 | 83 | 81 | 85 | 83 | 81 | 80 | 80 | 80 | 80 | 80 | 80 | 80 | | |
| 8 | 93 | 86 | 82 | 79 | 92 | 86 | 82 | 79 | 85 | 81 | 79 | 84 | 81 | 79 | 83 | 81 | 78 | 77 | 77 | 77 | 77 | 77 | 77 | 77 | | |
| 9 | 90 | 84 | 80 | 77 | 90 | 83 | 80 | 77 | 83 | 79 | 77 | 82 | 79 | 76 | 81 | 78 | 76 | 75 | 75 | 75 | 75 | 75 | 75 | 75 | | |
| 10 | 88 | 81 | 77 | 75 | 87 | 81 | 77 | 75 | 80 | 77 | 75 | 80 | 77 | 74 | 79 | 76 | 74 | 73 | 73 | 73 | 73 | 73 | 73 | 73 | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2010104 |
| 5° | 1916603 |
| 10° | 1554318 |
| 15° | 950177 |
| 20° | 415137 |
| 25° | 155307 |
| 30° | 64374 |
| 35° | 30114 |
| 40° | 13976 |
| 45° | 6838 |
| 50° | 3761 |
| 55° | 1376 |
| 60° | 493 |
| 65° | 584 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P498542

CATALOG NUMBER: LDA2B159027R30D010 2LBDL1MB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 345.2 | 33.3 |
| 10°-20° | 498.4 | 48.1 |
| 20°-30° | 148.8 | 14.3 |
| 30°-40° | 34.2 | 3.3 |
| 40°-50° | 8.4 | 0.8 |
| 50°-60° | 1.9 | 0.2 |
| 60°-70° | 0.3 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 992.4 | 95.7 |
| 0°-40° | 1026.6 | 99.0 |
| 0°-60° | 1036.9 | 100.0 |
| 0°-90° | 1037.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1037.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4074 | |
| 5° | 3870 | 345 |
| 15° | 1860 | 498 |
| 25° | 285 | 149 |
| 35° | 50 | 34 |
| 45° | 10 | 8 |
| 55° | 2 | 2 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P498542

CATALOG NUMBER: LDA2B159027R30D010 2LBDL1MB

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 4074.3 |
| 1° | 4065.1 |
| 2° | 4023.8 |
| 3° | 3996.1 |
| 4° | 3944.4 |
| 5° | 3870.0 |
| 6° | 3768.4 |
| 7° | 3647.2 |
| 8° | 3492.8 |
| 9° | 3304.8 |
| 10° | 3102.6 |
| 11° | 2886.3 |
| 12° | 2640.7 |
| 13° | 2376.6 |
| 14° | 2125.5 |
| 15° | 1860.3 |
| 16° | 1603.8 |
| 17° | 1351.0 |
| 18° | 1147.2 |
| 19° | 949.4 |
| 20° | 790.7 |
| 21° | 640.7 |
| 22.5° | 475.0 |
| 23° | 428.2 |
| 24° | 350.5 |
| 25° | 285.3 |
| 26° | 234.2 |
| 27° | 195.1 |
| 28° | 160.9 |
| 29° | 134.8 |
| 30° | 113.0 |
| 32.5° | 73.9 |
| 35° | 50.0 |
| 37.5° | 33.2 |
| 40° | 21.7 |
| 42.5° | 14.1 |
| 45° | 9.8 |
| 47.5° | 7.1 |
| 50° | 4.9 |
| 52.5° | 3.3 |
| 55° | 1.6 |
| 57.5° | 1.1 |
| 60° | 0.5 |
| 62.5° | 0.5 |
| 65° | 0.5 |



TEST NUMBER: P498542

CATALOG NUMBER: LDA2B159027R30D010 2LBDL1MB

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)