

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279625

Luminaire Tested: **LDA2B109730D010 EU2B10FL409730 2LBAD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109730D010 EU2B10FL409730 2LBAD1GPH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 849.4 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279625

CATALOG NUMBER: LDA2B109730D010 EU2B10FL409730 2LBAD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P279625

CATALOG NUMBER: LDA2B109730D010 EU2B10FL409730 2LBAD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89			
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82			
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72			
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1167985
5°	1143276
10°	1042023
15°	814007
20°	481973
25°	179150
30°	56000
35°	24874
40°	11528
45°	5442
50°	2993
55°	1634
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279625

CATALOG NUMBER: LDA2B109730D010 EU2B10FL409730 2LBAD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.4	25.1
10°-20°	424.4	50.0
20°-30°	173.8	20.5
30°-40°	28.8	3.4
40°-50°	6.8	0.8
50°-60°	1.8	0.2
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	811.6	95.5
0°-40°	840.3	98.9
0°-60°	848.9	99.9
0°-90°	849.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	849.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2367	
5°	2308	213
15°	1594	424
25°	329	174
35°	41	29
45°	8	7
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279625

CATALOG NUMBER: LDA2B109730D010 EU2B10FL409730 2LBAD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2367.4
1°	2359.2
2°	2348.3
3°	2338.6
4°	2325.7
5°	2308.5
6°	2283.2
7°	2250.0
8°	2202.9
9°	2145.5
10°	2080.0
11°	2004.0
12°	1918.2
13°	1820.3
14°	1711.5
15°	1593.7
17.5°	1263.8
20°	918.0
22.5°	587.7
25°	329.1
27.5°	173.5
30°	98.3
32.5°	62.4
35°	41.3
37.5°	27.3
40°	17.9
42.5°	11.7
45°	7.8
47.5°	5.5
50°	3.9
52.5°	2.7
55°	1.9
57.5°	1.2
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279625

CATALOG NUMBER: LDA2B109730D010 EU2B10FL409730 2LBAD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)