

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279630

Luminaire Tested: **LDA2B109730D010 EU2B10FL409730 2LBALD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279630  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B109730D010 EU2B10FL409730 2LBALD1WMH  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 844.5 lumens  
Efficiency: N/A  
Efficacy: 84.5 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279630

CATALOG NUMBER: LDA2B109730D010 EU2B10FL409730 2LBALD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P279630

CATALOG NUMBER: LDA2B109730D010 EU2B10FL409730 2LBALD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1161226
5°	1136689
10°	1036012
15°	809308
20°	479190
25°	178116
30°	55658
35°	24754
40°	11464
45°	5442
50°	2993
55°	1634
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279630

CATALOG NUMBER: LDA2B109730D010 EU2B10FL409730 2LBALD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	212.2	25.1
10°-20°	421.9	50.0
20°-30°	172.8	20.5
30°-40°	28.6	3.4
40°-50°	6.8	0.8
50°-60°	1.8	0.2
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	806.9	95.5
0°-40°	835.4	98.9
0°-60°	844.0	99.9
0°-90°	844.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	844.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2354	
5°	2295	212
15°	1584	422
25°	327	173
35°	41	29
45°	8	7
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279630

CATALOG NUMBER: LDA2B109730D010 EU2B10FL409730 2LBALD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2353.7
1°	2345.6
2°	2334.8
3°	2325.1
4°	2312.3
5°	2295.2
6°	2270.0
7°	2237.0
8°	2190.1
9°	2133.1
10°	2068.0
11°	1992.4
12°	1907.1
13°	1809.8
14°	1701.6
15°	1584.5
17.5°	1256.5
20°	912.7
22.5°	584.3
25°	327.2
27.5°	172.5
30°	97.7
32.5°	62.0
35°	41.1
37.5°	27.1
40°	17.8
42.5°	11.6
45°	7.8
47.5°	5.4
50°	3.9
52.5°	2.7
55°	1.9
57.5°	1.2
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279630

CATALOG NUMBER: LDA2B109730D010 EU2B10FL409730 2LBALD1WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)