

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498616

Luminaire Tested: **LDA2B159027R45D010 2LBDL1WMH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P498616  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159027R45D010 2LBDL1WMH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1049.6 lumens  
Efficiency: N/A  
Efficacy: 74.4 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P498616

CATALOG NUMBER: LDA2B159027R45D010 2LBDL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P498616

CATALOG NUMBER: LDA2B159027R45D010 2LBDL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1040303
5°	1017385
10°	943933
15°	804967
20°	606036
25°	365377
30°	176147
35°	79863
40°	36775
45°	18978
50°	9978
55°	3699
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P498616

CATALOG NUMBER: LDA2B159027R45D010 2LBDL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	191.0	18.2
10°-20°	430.4	41.0
20°-30°	307.5	29.3
30°-40°	92.2	8.8
40°-50°	22.9	2.2
50°-60°	4.8	0.5
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	928.9	88.5
0°-40°	1021.0	97.3
0°-60°	1048.7	99.9
0°-90°	1049.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1049.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2109	
5°	2054	191
15°	1576	430
25°	671	307
35°	133	92
45°	27	23
55°	4	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498616

CATALOG NUMBER: LDA2B159027R45D010 2LBDL1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2108.6
1°	2112.4
2°	2107.5
3°	2089.6
4°	2076.6
5°	2054.3
6°	2032.0
7°	2008.1
8°	1969.0
9°	1932.0
10°	1884.2
11°	1836.4
12°	1776.0
13°	1711.4
14°	1651.0
15°	1576.0
16°	1502.7
17°	1419.5
18°	1340.7
19°	1244.0
20°	1154.3
21°	1054.9
22.5°	906.5
23°	856.5
24°	759.2
25°	671.2
26°	583.1
27°	502.7
28°	427.7
29°	366.3
30°	309.2
32.5°	203.3
35°	132.6
37.5°	87.0
40°	57.1
42.5°	38.6
45°	27.2
47.5°	19.6
50°	13.0
52.5°	8.2
55°	4.3
57.5°	2.2
60°	1.1
62.5°	1.1
65°	0.5



TEST NUMBER: P498616

CATALOG NUMBER: LDA2B159027R45D010 2LBDL1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)