

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498617

Luminaire Tested: **LDA2B159027R45D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498617
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159027R45D010 2LBDLC1MB
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1123.3 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498617

CATALOG NUMBER: LDA2B159027R45D010 2LBDLC1MB

Luminous Intensity Polar Plot





TEST NUMBER: P498617

CATALOG NUMBER: LDA2B159027R45D010 2LBDLC1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1113320
5°	1088799
10°	1010161
15°	861457
20°	648563
25°	391017
30°	188509
35°	85464
40°	39351
45°	20304
50°	10745
55°	4043
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P498617

CATALOG NUMBER: LDA2B159027R45D010 2LBDLC1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	204.4	18.2
10°-20°	460.6	41.0
20°-30°	329.1	29.3
30°-40°	98.6	8.8
40°-50°	24.5	2.2
50°-60°	5.1	0.5
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	994.0	88.5
0°-40°	1092.7	97.3
0°-60°	1122.3	99.9
0°-90°	1123.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1123.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2257	
5°	2198	204
15°	1687	461
25°	718	329
35°	142	99
45°	29	24
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498617

CATALOG NUMBER: LDA2B159027R45D010 2LBDLC1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2256.6
1°	2260.7
2°	2255.5
3°	2236.3
4°	2222.3
5°	2198.5
6°	2174.6
7°	2149.0
8°	2107.1
9°	2067.6
10°	2016.4
11°	1965.2
12°	1900.7
13°	1831.5
14°	1766.9
15°	1686.6
16°	1608.1
17°	1519.1
18°	1434.8
19°	1331.3
20°	1235.3
21°	1128.9
22.5°	970.1
23°	916.6
24°	812.5
25°	718.3
26°	624.1
27°	538.0
28°	457.7
29°	392.0
30°	330.9
32.5°	217.5
35°	141.9
37.5°	93.1
40°	61.1
42.5°	41.3
45°	29.1
47.5°	20.9
50°	14.0
52.5°	8.7
55°	4.7
57.5°	2.3
60°	1.2
62.5°	1.2
65°	0.6



TEST NUMBER: P498617

CATALOG NUMBER: LDA2B159027R45D010 2LBDLC1MB

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)