

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278730

Luminaire Tested: **LDA2B109730D010 EU2B10NFL259730 2LBALD1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278730  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B109730D010 EU2B10NFL259730 2LBALD1LI  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl w/lens Self-Flanged, H  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 782.6 lumens  
Efficiency: N/A  
Efficacy: 78.3 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278730

CATALOG NUMBER: LDA2B109730D010 EU2B10NFL259730 2LBALD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P278730

CATALOG NUMBER: LDA2B109730D010 EU2B10NFL259730 2LBALD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97						97													
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94						94													
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91						91													
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89						89													
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86						86													
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84						84													
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82						82													
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80						80													
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78						78													
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76						76													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2003049
5°	1847318
10°	1244867
15°	613787
20°	262145
25°	103048
30°	40562
35°	17767
40°	8566
45°	4117
50°	2303
55°	1290
60°	691
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P278730

CATALOG NUMBER: LDA2B109730D010 EU2B10NFL259730 2LBALD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	316.0	40.4
10°-20°	340.3	43.5
20°-30°	98.3	12.6
30°-40°	20.7	2.6
40°-50°	5.1	0.7
50°-60°	1.5	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.5	96.4
0°-40°	775.2	99.1
0°-60°	781.8	99.9
0°-90°	782.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	782.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4060	
5°	3730	316
15°	1202	340
25°	189	98
35°	30	21
45°	6	5
55°	2	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278730

CATALOG NUMBER: LDA2B109730D010 EU2B10NFL259730 2LBALD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4060.0
1°	4034.6
2°	3991.4
3°	3933.1
4°	3850.4
5°	3730.1
6°	3567.7
7°	3355.9
8°	3095.3
9°	2791.6
10°	2484.9
11°	2174.9
12°	1882.2
13°	1622.4
14°	1393.9
15°	1201.7
17.5°	794.2
20°	499.3
22.5°	307.1
25°	189.3
27.5°	115.5
30°	71.2
32.5°	45.0
35°	29.5
37.5°	19.6
40°	13.3
42.5°	9.2
45°	5.9
47.5°	3.7
50°	3.0
52.5°	2.2
55°	1.5
57.5°	1.1
60°	0.7
62.5°	0.7
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P278730

CATALOG NUMBER: LDA2B109730D010 EU2B10NFL259730 2LBALD1LI

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)