

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498618

Luminaire Tested: **LDA2B159027R45D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P498618  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159027R45D010 2LBDLC1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1123.3 lumens  
Efficiency: N/A  
Efficacy: 79.7 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P498618

CATALOG NUMBER: LDA2B159027R45D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P498618

CATALOG NUMBER: LDA2B159027R45D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1113320
5°	1088799
10°	1010161
15°	861457
20°	648563
25°	391017
30°	188509
35°	85464
40°	39351
45°	20304
50°	10745
55°	4043
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P498618

CATALOG NUMBER: LDA2B159027R45D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	204.4	18.2
10°-20°	460.6	41.0
20°-30°	329.1	29.3
30°-40°	98.6	8.8
40°-50°	24.5	2.2
50°-60°	5.1	0.5
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	994.0	88.5
0°-40°	1092.7	97.3
0°-60°	1122.3	99.9
0°-90°	1123.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1123.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2257	
5°	2198	204
15°	1687	461
25°	718	329
35°	142	99
45°	29	24
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498618

CATALOG NUMBER: LDA2B159027R45D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2256.6
1°	2260.7
2°	2255.5
3°	2236.3
4°	2222.3
5°	2198.5
6°	2174.6
7°	2149.0
8°	2107.1
9°	2067.6
10°	2016.4
11°	1965.2
12°	1900.7
13°	1831.5
14°	1766.9
15°	1686.6
16°	1608.1
17°	1519.1
18°	1434.8
19°	1331.3
20°	1235.3
21°	1128.9
22.5°	970.1
23°	916.6
24°	812.5
25°	718.3
26°	624.1
27°	538.0
28°	457.7
29°	392.0
30°	330.9
32.5°	217.5
35°	141.9
37.5°	93.1
40°	61.1
42.5°	41.3
45°	29.1
47.5°	20.9
50°	14.0
52.5°	8.7
55°	4.7
57.5°	2.3
60°	1.2
62.5°	1.2
65°	0.6



TEST NUMBER: P498618

CATALOG NUMBER: LDA2B159027R45D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)