

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498629

Luminaire Tested: **LDA2B159027R60D010 2LBD1WMH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P498629  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159027R60D010 2LBD1WMH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1072.5 lumens  
Efficiency: N/A  
Efficacy: 76.1 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P498629

CATALOG NUMBER: LDA2B159027R60D010 2LBD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P498629

CATALOG NUMBER: LDA2B159027R60D010 2LBD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	642160
5°	609599
10°	596809
15°	577625
20°	528122
25°	468916
30°	350755
35°	198031
40°	74580
45°	33351
50°	16272
55°	3269
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P498629

CATALOG NUMBER: LDA2B159027R60D010 2LBD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.5	10.9
10°-20°	314.1	29.3
20°-30°	383.8	35.8
30°-40°	209.3	19.5
40°-50°	41.9	3.9
50°-60°	6.0	0.6
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.4	75.9
0°-40°	1023.8	95.5
0°-60°	1071.6	99.9
0°-90°	1072.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1072.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1302	
5°	1231	117
15°	1131	314
25°	861	384
35°	329	209
45°	48	42
55°	4	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498629

CATALOG NUMBER: LDA2B159027R60D010 2LBD1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1301.6
1°	1295.6
2°	1284.2
3°	1269.0
4°	1247.2
5°	1230.9
6°	1222.2
7°	1211.9
8°	1203.8
9°	1200.0
10°	1191.3
11°	1181.5
12°	1172.8
13°	1162.5
14°	1147.2
15°	1130.9
16°	1110.3
17°	1081.5
18°	1063.0
19°	1033.1
20°	1005.9
21°	980.9
22.5°	939.1
23°	921.7
24°	895.1
25°	861.4
26°	818.5
27°	773.3
28°	721.7
29°	672.8
30°	615.7
32.5°	472.3
35°	328.8
37.5°	206.0
40°	115.8
42.5°	72.3
45°	47.8
47.5°	32.6
50°	21.2
52.5°	10.9
55°	3.8
57.5°	1.6
60°	1.1
62.5°	1.1
65°	0.5



TEST NUMBER: P498629

CATALOG NUMBER: LDA2B159027R60D010 2LBD1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)