

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498683

Luminaire Tested: **LDA2B159027R70D010 2LBDL1WH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P498683  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159027R70D010 2LBDL1WH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 986.7 lumens  
Efficiency: N/A  
Efficacy: 70.0 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P498683

CATALOG NUMBER: LDA2B159027R70D010 2LBDL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P498683

CATALOG NUMBER: LDA2B159027R70D010 2LBDL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	47	66	57	50	46	56	50	46		55	50	46		54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	390644
5°	388372
10°	385799
15°	378631
20°	364945
25°	349373
30°	332810
35°	274641
40°	178527
45°	93285
50°	43366
55°	15913
60°	1579
65°	1284
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P498683

CATALOG NUMBER: LDA2B159027R70D010 2LBDL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.2	7.5
10°-20°	208.3	21.1
20°-30°	295.7	30.0
30°-40°	276.5	28.0
40°-50°	111.2	11.3
50°-60°	19.4	2.0
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	578.1	58.6
0°-40°	854.6	86.6
0°-60°	985.3	99.9
0°-90°	986.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	986.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	792	
5°	784	74
15°	741	208
25°	642	296
35°	456	276
45°	134	111
55°	18	19
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498683

CATALOG NUMBER: LDA2B159027R70D010 2LBDL1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	791.8
1°	792.9
2°	791.3
3°	788.0
4°	786.4
5°	784.2
6°	775.5
7°	778.2
8°	770.6
9°	769.0
10°	770.1
11°	763.0
12°	761.4
13°	752.7
14°	749.4
15°	741.3
16°	736.4
17°	726.6
18°	715.2
19°	708.7
20°	695.1
21°	684.8
22.5°	665.7
23°	660.8
24°	651.6
25°	641.8
26°	634.2
27°	623.4
28°	612.5
29°	599.4
30°	584.2
32.5°	531.0
35°	456.0
37.5°	367.4
40°	277.2
42.5°	197.8
45°	133.7
47.5°	88.0
50°	56.5
52.5°	35.3
55°	18.5
57.5°	6.0
60°	1.6
62.5°	1.1
65°	1.1



TEST NUMBER: P498683

CATALOG NUMBER: LDA2B159027R70D010 2LBDL1WH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)