

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497165

Luminaire Tested: **LDA2B109730R70D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P497165  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109730R70D010 2LBDL1GPH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 710.2 lumens  
Efficiency: N/A  
Efficacy: 71.0 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P497165

CATALOG NUMBER: LDA2B109730R70D010 2LBDL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P497165

CATALOG NUMBER: LDA2B109730R70D010 2LBDL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	281167
5°	279517
10°	277639
15°	272494
20°	262670
25°	251442
30°	239553
35°	197669
40°	128486
45°	67121
50°	31239
55°	11440
60°	1184
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P497165

CATALOG NUMBER: LDA2B109730R70D010 2LBDL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.4	7.5
10°-20°	149.9	21.1
20°-30°	212.8	30.0
30°-40°	199.0	28.0
40°-50°	80.0	11.3
50°-60°	14.0	2.0
60°-70°	0.7	0.1
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	416.1	58.6
0°-40°	615.1	86.6
0°-60°	709.1	99.9
0°-90°	710.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	710.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	570	
5°	564	53
15°	534	150
25°	462	213
35°	328	199
45°	96	80
55°	13	14
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497165

CATALOG NUMBER: LDA2B109730R70D010 2LBDL1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	569.9
1°	570.7
2°	569.5
3°	567.1
4°	566.0
5°	564.4
6°	558.1
7°	560.1
8°	554.6
9°	553.4
10°	554.2
11°	549.1
12°	548.0
13°	541.7
14°	539.4
15°	533.5
16°	530.0
17°	522.9
18°	514.7
19°	510.0
20°	500.3
21°	492.8
22.5°	479.1
23°	475.6
24°	469.0
25°	461.9
26°	456.4
27°	448.6
28°	440.8
29°	431.4
30°	420.5
32.5°	382.1
35°	328.2
37.5°	264.4
40°	199.5
42.5°	142.4
45°	96.2
47.5°	63.4
50°	40.7
52.5°	25.4
55°	13.3
57.5°	4.3
60°	1.2
62.5°	0.8
65°	0.8



TEST NUMBER: P497165

CATALOG NUMBER: LDA2B109730R70D010 2LBDL1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)