

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278909

Luminaire Tested: **LDA2B159040D010 EU2B15NFL259040 2LBALD1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278909
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159040D010 EU2B15NFL259040 2LBALD1B
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, B
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1202.8 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278909

CATALOG NUMBER: LDA2B159040D010 EU2B15NFL259040 2LBALD1B

Luminous Intensity Polar Plot





TEST NUMBER: P278909

CATALOG NUMBER: LDA2B159040D010 EU2B15NFL259040 2LBALD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97				97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94				94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91				91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89				89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86				86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84				84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82				82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80				80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78				78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76				76															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3078627
5°	2839247
10°	1913315
15°	943333
20°	402956
25°	158410
30°	62381
35°	27344
40°	13138
45°	6349
50°	3454
55°	1978
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P278909

CATALOG NUMBER: LDA2B159040D010 EU2B15NFL259040 2LBALD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	485.6	40.4
10°-20°	523.0	43.5
20°-30°	151.0	12.6
30°-40°	31.9	2.7
40°-50°	7.9	0.7
50°-60°	2.3	0.2
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1159.6	96.4
0°-40°	1191.5	99.1
0°-60°	1201.6	99.9
0°-90°	1202.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1202.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6240	
5°	5733	486
15°	1847	523
25°	291	151
35°	45	32
45°	9	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278909

CATALOG NUMBER: LDA2B159040D010 EU2B15NFL259040 2LBALD1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6240.1
1°	6201.0
2°	6134.6
3°	6045.0
4°	5917.9
5°	5733.0
6°	5483.4
7°	5157.8
8°	4757.4
9°	4290.5
10°	3819.2
11°	3342.7
12°	2892.9
13°	2493.5
14°	2142.4
15°	1846.9
17.5°	1220.7
20°	767.5
22.5°	471.9
25°	291.0
27.5°	177.5
30°	109.5
32.5°	69.2
35°	45.4
37.5°	30.1
40°	20.4
42.5°	14.2
45°	9.1
47.5°	5.7
50°	4.5
52.5°	3.4
55°	2.3
57.5°	1.7
60°	1.1
62.5°	1.1
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.6
80°	0.0
82.5°	0.0



TEST NUMBER: P278909

CATALOG NUMBER: LDA2B159040D010 EU2B15NFL259040 2LBALD1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)