

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278156

Luminaire Tested: **LDA2B159040D010 EU2B15SP159040 2LBAD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278156
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159040D010 EU2B15SP159040 2LBAD1MW
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1231.1 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278156

CATALOG NUMBER: LDA2B159040D010 EU2B15SP159040 2LBAD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P278156

CATALOG NUMBER: LDA2B159040D010 EU2B15SP159040 2LBAD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98			
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96			
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93			
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92			
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90			
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88			
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86			
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85			
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83			
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5561766
5°	4434188
10°	1925088
15°	665119
20°	272698
25°	123190
30°	49563
35°	23067
40°	12559
45°	4675
50°	2763
55°	2064
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P278156

CATALOG NUMBER: LDA2B159040D010 EU2B15SP159040 2LBAD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	676.7	55.0
10°-20°	406.4	33.0
20°-30°	111.9	9.1
30°-40°	26.6	2.2
40°-50°	6.6	0.5
50°-60°	2.1	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1194.9	97.1
0°-40°	1221.5	99.2
0°-60°	1230.2	99.9
0°-90°	1231.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1231.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11273	
5°	8954	677
15°	1302	406
25°	226	112
35°	38	27
45°	7	7
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278156

CATALOG NUMBER: LDA2B159040D010 EU2B15SP159040 2LBAD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	11273.2
1°	11148.5
2°	10849.9
3°	10394.3
4°	9751.5
5°	8953.5
6°	7979.1
7°	6911.7
8°	5790.2
9°	4758.6
10°	3842.7
11°	3067.2
12°	2441.4
13°	1968.8
14°	1592.9
15°	1302.2
17.5°	808.3
20°	519.4
22.5°	340.6
25°	226.3
27.5°	145.4
30°	87.0
32.5°	54.7
35°	38.3
37.5°	28.0
40°	19.5
42.5°	11.6
45°	6.7
47.5°	4.9
50°	3.6
52.5°	3.0
55°	2.4
57.5°	1.8
60°	1.2
62.5°	1.2
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P278156

CATALOG NUMBER: LDA2B159040D010 EU2B15SP159040 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)