

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278752

Luminaire Tested: **LDA2B10D2WD010 EU2B10NFL25D2W 2LBALD1WHH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B10D2WD010 EU2B10NFL25D2W 2LBALD1WHH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, WHH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 790.8 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278752

CATALOG NUMBER: LDA2B10D2WD010 EU2B10NFL25D2W 2LBALD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P278752

CATALOG NUMBER: LDA2B10D2WD010 EU2B10NFL25D2W 2LBALD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100													
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97	97	97	97													
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94	94	94	94													
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91	91	91	91													
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89	89	89													
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86	86	86													
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84	84	84													
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82	82	82													
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80	80	80													
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78													
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76	76	76	76													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2024066
5°	1866683
10°	1257942
15°	620223
20°	264927
25°	104137
30°	41017
35°	17948
40°	8630
45°	4186
50°	2303
55°	1290
60°	691
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P278752

CATALOG NUMBER: LDA2B10D2WD010 EU2B10NFL25D2W 2LBALD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.3	40.4
10°-20°	343.9	43.5
20°-30°	99.3	12.6
30°-40°	21.0	2.7
40°-50°	5.2	0.7
50°-60°	1.5	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.4	96.4
0°-40°	783.4	99.1
0°-60°	790.0	99.9
0°-90°	790.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	790.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4103	
5°	3769	319
15°	1214	344
25°	191	99
35°	30	21
45°	6	5
55°	2	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278752

CATALOG NUMBER: LDA2B10D2WD010 EU2B10NFL25D2W 2LBALD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4102.6
1°	4076.9
2°	4033.3
3°	3974.3
4°	3890.8
5°	3769.2
6°	3605.1
7°	3391.1
8°	3127.8
9°	2820.9
10°	2511.0
11°	2197.7
12°	1902.0
13°	1639.4
14°	1408.6
15°	1214.3
17.5°	802.6
20°	504.6
22.5°	310.3
25°	191.3
27.5°	116.7
30°	72.0
32.5°	45.5
35°	29.8
37.5°	19.8
40°	13.4
42.5°	9.3
45°	6.0
47.5°	3.7
50°	3.0
52.5°	2.2
55°	1.5
57.5°	1.1
60°	0.7
62.5°	0.7
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P278752

CATALOG NUMBER: LDA2B10D2WD010 EU2B10NFL25D2W 2LBALD1WHH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)