

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498870

Luminaire Tested: **LDA2B159030R65D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498870
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159030R65D010 2LBDL1GPH
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1061.3 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498870
CATALOG NUMBER: LDA2B159030R65D010 2LBDL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P498870

CATALOG NUMBER: LDA2B159030R65D010 2LBDL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93					93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87					87			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80					80			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74					74			
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69					69			
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64					64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60					60			
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56					56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52					52			
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49					49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	555279
5°	532093
10°	506734
15°	481601
20°	448004
25°	413608
30°	358845
35°	257476
40°	139885
45°	59725
50°	25712
55°	9290
60°	1677
65°	1284
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P498870

CATALOG NUMBER: LDA2B159030R65D010 2LBDL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.6	9.5
10°-20°	264.1	24.9
20°-30°	345.3	32.5
30°-40°	262.7	24.8
40°-50°	76.0	7.2
50°-60°	11.4	1.1
60°-70°	1.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	710.0	66.9
0°-40°	972.7	91.7
0°-60°	1060.1	99.9
0°-90°	1061.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1061.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1126	
5°	1074	101
15°	943	264
25°	760	345
35°	428	263
45°	86	76
55°	11	11
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498870

CATALOG NUMBER: LDA2B159030R65D010 2LBDL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1125.5
1°	1121.5
2°	1115.3
3°	1102.8
4°	1089.2
5°	1074.4
6°	1060.3
7°	1047.8
8°	1035.9
9°	1025.1
10°	1011.5
11°	999.6
12°	987.1
13°	974.7
14°	961.0
15°	942.9
16°	929.3
17°	912.9
18°	887.9
19°	874.9
20°	853.3
21°	834.0
22.5°	804.6
23°	793.2
24°	775.6
25°	759.8
26°	738.8
27°	715.5
28°	690.0
29°	662.8
30°	629.9
32.5°	539.8
35°	427.5
37.5°	315.2
40°	217.2
42.5°	137.8
45°	85.6
47.5°	53.3
50°	33.5
52.5°	19.8
55°	10.8
57.5°	4.0
60°	1.7
62.5°	1.1
65°	1.1



TEST NUMBER: P498870

CATALOG NUMBER: LDA2B159030R65D010 2LBDL1GPH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)