

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498890

Luminaire Tested: **LDA2B159030R70D010 2LBD1WHH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P498890  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159030R70D010 2LBD1WHH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1111.8 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P498890

CATALOG NUMBER: LDA2B159030R70D010 2LBD1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P498890

CATALOG NUMBER: LDA2B159030R70D010 2LBD1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50		59	54	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	434405
5°	429626
10°	427480
15°	425979
20°	410779
25°	393848
30°	389892
35°	332942
40°	207767
45°	96146
50°	34846
55°	2408
60°	1085
65°	1284
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P498890

CATALOG NUMBER: LDA2B159030R70D010 2LBD1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.3	7.4
10°-20°	233.6	21.0
20°-30°	335.9	30.2
30°-40°	331.1	29.8
40°-50°	118.0	10.6
50°-60°	9.7	0.9
60°-70°	0.9	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	651.8	58.6
0°-40°	982.9	88.4
0°-60°	1110.5	99.9
0°-90°	1111.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1111.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	880	
5°	868	82
15°	834	234
25°	724	336
35°	553	331
45°	138	118
55°	3	10
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P498890

CATALOG NUMBER: LDA2B159030R70D010 2LBD1WHH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	880.5
1°	880.5
2°	878.8
3°	879.4
4°	872.0
5°	867.5
6°	861.3
7°	859.0
8°	856.2
9°	855.6
10°	853.3
11°	850.5
12°	850.5
13°	845.4
14°	838.6
15°	834.0
16°	825.0
17°	819.9
18°	804.0
19°	793.2
20°	782.4
21°	768.3
22.5°	748.4
23°	740.5
24°	733.1
25°	723.5
26°	717.8
27°	708.2
28°	707.0
29°	696.8
30°	684.4
32.5°	636.2
35°	552.8
37.5°	444.5
40°	322.6
42.5°	220.6
45°	137.8
47.5°	82.2
50°	45.4
52.5°	17.0
55°	2.8
57.5°	1.7
60°	1.1
62.5°	1.1
65°	1.1



TEST NUMBER: P498890

CATALOG NUMBER: LDA2B159030R70D010 2LBD1WHH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)