

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498897

Luminaire Tested: **LDA2B159030R70D010 2LBDL1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159030R70D010 2LBDL1MMS
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1029.5 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498897

CATALOG NUMBER: LDA2B159030R70D010 2LBDL1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P498897

CATALOG NUMBER: LDA2B159030R70D010 2LBDL1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	407566
5°	405211
10°	402481
15°	395026
20°	380748
25°	364506
30°	347223
35°	286506
40°	186256
45°	97332
50°	45285
55°	16601
60°	1677
65°	1284
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P498897

CATALOG NUMBER: LDA2B159030R70D010 2LBDL1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	7.5
10°-20°	217.3	21.1
20°-30°	308.5	30.0
30°-40°	288.5	28.0
40°-50°	116.0	11.3
50°-60°	20.3	2.0
60°-70°	1.0	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	603.2	58.6
0°-40°	891.7	86.6
0°-60°	1028.0	99.9
0°-90°	1029.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1029.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	826	
5°	818	77
15°	773	217
25°	670	308
35°	476	288
45°	140	116
55°	19	20
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P498897

CATALOG NUMBER: LDA2B159030R70D010 2LBDL1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	826.1
1°	827.2
2°	825.5
3°	822.1
4°	820.4
5°	818.2
6°	809.1
7°	811.9
8°	804.0
9°	802.3
10°	803.4
11°	796.1
12°	794.4
13°	785.3
14°	781.9
15°	773.4
16°	768.3
17°	758.1
18°	746.2
19°	739.4
20°	725.2
21°	714.4
22.5°	694.6
23°	689.5
24°	679.8
25°	669.6
26°	661.7
27°	650.3
28°	639.0
29°	625.4
30°	609.5
32.5°	554.0
35°	475.7
37.5°	383.3
40°	289.2
42.5°	206.4
45°	139.5
47.5°	91.9
50°	59.0
52.5°	36.9
55°	19.3
57.5°	6.2
60°	1.7
62.5°	1.1
65°	1.1



TEST NUMBER: P498897

CATALOG NUMBER: LDA2B159030R70D010 2LBDL1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)