

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497374

Luminaire Tested: **LDA2B158027R70D010 2LBD1MB**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P497374  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B158027R70D010 2LBD1MB  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1352.4 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P497374

CATALOG NUMBER: LDA2B158027R70D010 2LBD1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P497374

CATALOG NUMBER: LDA2B158027R70D010 2LBD1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75	82	78	74	80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50	59	54	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	528390
5°	522534
10°	519960
15°	518172
20°	499666
25°	479041
30°	474206
35°	404975
40°	252721
45°	116938
50°	42368
55°	2925
60°	1381
65°	1634
70°	1010
75°	1334
80°	0
85°	0



TEST NUMBER: P497374

CATALOG NUMBER: LDA2B158027R70D010 2LBD1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.1	7.4
10°-20°	284.1	21.0
20°-30°	408.5	30.2
30°-40°	402.7	29.8
40°-50°	143.5	10.6
50°-60°	11.8	0.9
60°-70°	1.1	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	792.8	58.6
0°-40°	1195.5	88.4
0°-60°	1350.8	99.9
0°-90°	1352.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1352.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1071	
5°	1055	100
15°	1014	284
25°	880	409
35°	672	403
45°	168	144
55°	3	12
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P497374

CATALOG NUMBER: LDA2B158027R70D010 2LBD1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1071.0
1°	1071.0
2°	1068.9
3°	1069.6
4°	1060.7
5°	1055.1
6°	1047.6
7°	1044.8
8°	1041.3
9°	1040.7
10°	1037.9
11°	1034.5
12°	1034.5
13°	1028.2
14°	1020.0
15°	1014.5
16°	1003.4
17°	997.2
18°	977.9
19°	964.8
20°	951.7
21°	934.5
22.5°	910.3
23°	900.7
24°	891.7
25°	880.0
26°	873.1
27°	861.4
28°	860.0
29°	847.6
30°	832.4
32.5°	773.8
35°	672.4
37.5°	540.7
40°	392.4
42.5°	268.3
45°	167.6
47.5°	100.0
50°	55.2
52.5°	20.7
55°	3.4
57.5°	2.1
60°	1.4
62.5°	1.4
65°	1.4



TEST NUMBER: P497374

CATALOG NUMBER: LDA2B158027R70D010 2LBD1MB

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)