

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279810

Luminaire Tested: **LDA2B159050D010 EU2B15FL409050 2LBAD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279810
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159050D010 EU2B15FL409050 2LBAD1H
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1360.9 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279810

CATALOG NUMBER: LDA2B159050D010 EU2B15FL409050 2LBAD1H

Luminous Intensity Polar Plot





TEST NUMBER: P279810

CATALOG NUMBER: LDA2B159050D010 EU2B15FL409050 2LBAD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89			
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82			
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72			
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	73	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1871420
5°	1831867
10°	1669642
15°	1304291
20°	772206
25°	287043
30°	89725
35°	39871
40°	18484
45°	8721
50°	4759
55°	2666
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P279810

CATALOG NUMBER: LDA2B159050D010 EU2B15FL409050 2LBAD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	341.9	25.1
10°-20°	679.9	50.0
20°-30°	278.5	20.5
30°-40°	46.1	3.4
40°-50°	10.9	0.8
50°-60°	2.9	0.2
60°-70°	0.7	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1300.3	95.5
0°-40°	1346.4	98.9
0°-60°	1360.2	99.9
0°-90°	1360.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1360.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3793	
5°	3699	342
15°	2554	680
25°	527	278
35°	66	46
45°	12	11
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279810

CATALOG NUMBER: LDA2B159050D010 EU2B15FL409050 2LBAD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3793.2
1°	3780.1
2°	3762.6
3°	3747.0
4°	3726.4
5°	3698.9
6°	3658.3
7°	3605.2
8°	3529.6
9°	3437.7
10°	3332.8
11°	3210.9
12°	3073.5
13°	2916.6
14°	2742.3
15°	2553.6
17.5°	2025.0
20°	1470.8
22.5°	941.6
25°	527.3
27.5°	278.0
30°	157.5
32.5°	100.0
35°	66.2
37.5°	43.7
40°	28.7
42.5°	18.7
45°	12.5
47.5°	8.7
50°	6.2
52.5°	4.4
55°	3.1
57.5°	1.9
60°	1.2
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279810

CATALOG NUMBER: LDA2B159050D010 EU2B15FL409050 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)