

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497388

Luminaire Tested: **LDA2B158027R70D010 2LBDL1WHH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497388
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158027R70D010 2LBDL1WHH
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1252.1 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497388

CATALOG NUMBER: LDA2B158027R70D010 2LBDL1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P497388

CATALOG NUMBER: LDA2B158027R70D010 2LBDL1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93					93			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85					85			
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78					78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72					72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66					66			
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61					61			
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56					56			
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52					52			
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48					48			
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45					45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	495730
5°	492820
10°	489551
15°	480477
20°	463072
25°	443385
30°	422365
35°	348481
40°	226508
45°	118403
50°	55032
55°	20128
60°	2072
65°	1634
70°	1010
75°	1334
80°	0
85°	0



TEST NUMBER: P497388

CATALOG NUMBER: LDA2B158027R70D010 2LBDL1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	7.5
10°-20°	264.3	21.1
20°-30°	375.2	30.0
30°-40°	350.9	28.0
40°-50°	141.1	11.3
50°-60°	24.7	2.0
60°-70°	1.2	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	733.7	58.6
0°-40°	1084.5	86.6
0°-60°	1250.3	99.9
0°-90°	1252.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1252.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1005	
5°	995	94
15°	941	264
25°	814	375
35°	579	351
45°	170	141
55°	23	25
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P497388

CATALOG NUMBER: LDA2B158027R70D010 2LBDL1WHH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1004.8
1°	1006.2
2°	1004.1
3°	1000.0
4°	997.9
5°	995.1
6°	984.1
7°	987.6
8°	977.9
9°	975.8
10°	977.2
11°	968.2
12°	966.2
13°	955.1
14°	951.0
15°	940.7
16°	934.5
17°	922.0
18°	907.6
19°	899.3
20°	882.0
21°	868.9
22.5°	844.8
23°	838.6
24°	826.9
25°	814.5
26°	804.8
27°	791.0
28°	777.2
29°	760.7
30°	741.4
32.5°	673.8
35°	578.6
37.5°	466.2
40°	351.7
42.5°	251.0
45°	169.7
47.5°	111.7
50°	71.7
52.5°	44.8
55°	23.4
57.5°	7.6
60°	2.1
62.5°	1.4
65°	1.4



TEST NUMBER: P497388

CATALOG NUMBER: LDA2B158027R70D010 2LBDL1WHH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)