

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315103

Luminaire Tested: **LDA2B15NFL9050D010 PIN1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B15NFL9050D010 PIN1MB
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, Black oculus black finish
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1147.4 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315103
CATALOG NUMBER: LDA2B15NFL9050D010 PIN1MB

Luminous Intensity Polar Plot





TEST NUMBER: P315103

CATALOG NUMBER: LDA2B15NFL9050D010 PIN1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76	76	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2937131
5°	2708750
10°	1825344
15°	899969
20°	384423
25°	151116
30°	59475
35°	26079
40°	12559
45°	6070
50°	3300
55°	1892
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P315103

CATALOG NUMBER: LDA2B15NFL9050D010 PIN1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	463.3	40.4
10°-20°	499.0	43.5
20°-30°	144.1	12.6
30°-40°	30.4	2.7
40°-50°	7.5	0.7
50°-60°	2.1	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1106.3	96.4
0°-40°	1136.7	99.1
0°-60°	1146.4	99.9
0°-90°	1147.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1147.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5953	
5°	5470	463
15°	1762	499
25°	278	144
35°	43	30
45°	9	7
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315103

CATALOG NUMBER: LDA2B15NFL9050D010 PIN1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	5953.3
1°	5915.9
2°	5852.6
3°	5767.1
4°	5645.9
5°	5469.5
6°	5231.4
7°	4920.7
8°	4538.7
9°	4093.3
10°	3643.6
11°	3189.0
12°	2759.9
13°	2378.9
14°	2043.9
15°	1762.0
17.5°	1164.6
20°	732.2
22.5°	450.2
25°	277.6
27.5°	169.4
30°	104.4
32.5°	66.0
35°	43.3
37.5°	28.7
40°	19.5
42.5°	13.5
45°	8.7
47.5°	5.4
50°	4.3
52.5°	3.2
55°	2.2
57.5°	1.6
60°	1.1
62.5°	1.1
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P315103

CATALOG NUMBER: LDA2B15NFL9050D010 PIN1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)