

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315102

Luminaire Tested: **LDA2B15NFL9050D010 PINW1MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P315102  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B15NFL9050D010 PINW1MMS  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in Adj PinHole, White oculus, matte metallic silver finish  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1159.9 lumens  
Efficiency: N/A  
Efficacy: 82.3 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P315102

CATALOG NUMBER: LDA2B15NFL9050D010 PINW1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P315102

CATALOG NUMBER: LDA2B15NFL9050D010 PINW1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100										100																		
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97										97																		
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94										94																		
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91										91																		
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89										89																		
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86										86																		
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84										84																		
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82										82																		
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80										80																		
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78										78																		
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76										76																		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2968903
5°	2738068
10°	1845133
15°	909725
20°	388571
25°	152749
30°	60159
35°	26380
40°	12688
45°	6140
50°	3377
55°	1892
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P315102

CATALOG NUMBER: LDA2B15NFL9050D010 PINW1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	468.3	40.4
10°-20°	504.4	43.5
20°-30°	145.6	12.6
30°-40°	30.7	2.7
40°-50°	7.6	0.7
50°-60°	2.2	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1118.3	96.4
0°-40°	1149.1	99.1
0°-60°	1158.8	99.9
0°-90°	1159.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1159.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6018	
5°	5529	468
15°	1781	504
25°	281	146
35°	44	31
45°	9	8
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315102

CATALOG NUMBER: LDA2B15NFL9050D010 PINW1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6017.7
1°	5980.0
2°	5916.0
3°	5829.6
4°	5707.0
5°	5528.7
6°	5288.0
7°	4974.0
8°	4587.8
9°	4137.6
10°	3683.1
11°	3223.6
12°	2789.8
13°	2404.7
14°	2066.1
15°	1781.1
17.5°	1177.2
20°	740.1
22.5°	455.1
25°	280.6
27.5°	171.2
30°	105.6
32.5°	66.7
35°	43.8
37.5°	29.0
40°	19.7
42.5°	13.7
45°	8.8
47.5°	5.5
50°	4.4
52.5°	3.3
55°	2.2
57.5°	1.6
60°	1.1
62.5°	1.1
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P315102

CATALOG NUMBER: LDA2B15NFL9050D010 PINW1MMS

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)