

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278862

Luminaire Tested: **LDA2B159027D010 EU2B15NFL259027 2LBALD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278862  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B159027D010 EU2B15NFL259027 2LBALD1WMH  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl w/lens Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1087.3 lumens  
Efficiency: N/A  
Efficacy: 77.1 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278862

CATALOG NUMBER: LDA2B159027D010 EU2B15NFL259027 2LBALD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P278862

CATALOG NUMBER: LDA2B159027D010 EU2B15NFL259027 2LBALD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97				97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94				94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91				91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89				89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86				86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84				84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82				82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80				80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78				78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76				76															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2783202
5°	2566812
10°	1729708
15°	852826
20°	364262
25°	143222
30°	56399
35°	24694
40°	11915
45°	5721
50°	3147
55°	1806
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P278862

CATALOG NUMBER: LDA2B159027D010 EU2B15NFL259027 2LBALD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	439.0	40.4
10°-20°	472.8	43.5
20°-30°	136.5	12.6
30°-40°	28.8	2.7
40°-50°	7.1	0.7
50°-60°	2.0	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1048.4	96.4
0°-40°	1077.2	99.1
0°-60°	1086.3	99.9
0°-90°	1087.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1087.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5641	
5°	5183	439
15°	1670	473
25°	263	137
35°	41	29
45°	8	7
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278862

CATALOG NUMBER: LDA2B159027D010 EU2B15NFL259027 2LBALD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5641.3
1°	5606.0
2°	5546.0
3°	5464.9
4°	5350.1
5°	5182.9
6°	4957.3
7°	4662.9
8°	4300.9
9°	3878.8
10°	3452.7
11°	3021.9
12°	2615.3
13°	2254.3
14°	1936.9
15°	1669.7
17.5°	1103.5
20°	693.8
22.5°	426.7
25°	263.1
27.5°	160.5
30°	99.0
32.5°	62.6
35°	41.0
37.5°	27.2
40°	18.5
42.5°	12.8
45°	8.2
47.5°	5.1
50°	4.1
52.5°	3.1
55°	2.1
57.5°	1.5
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P278862

CATALOG NUMBER: LDA2B159027D010 EU2B15NFL259027 2LBALD1WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)