

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280657

Luminaire Tested: **LDA2B159027D010 EU2B15WFL559027 2LBALD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159027D010 EU2B15WFL559027 2LBALD1GPH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1164.9 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280657

CATALOG NUMBER: LDA2B159027D010 EU2B15WFL559027 2LBALD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P280657

CATALOG NUMBER: LDA2B159027D010 EU2B15WFL559027 2LBALD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	994913
5°	974645
10°	906360
15°	791329
20°	655178
25°	501088
30°	274189
35°	101485
40°	35164
45°	15838
50°	7445
55°	3699
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P280657

CATALOG NUMBER: LDA2B159027D010 EU2B15WFL559027 2LBALD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.9	15.7
10°-20°	428.2	36.8
20°-30°	404.7	34.7
30°-40°	124.6	10.7
40°-50°	19.7	1.7
50°-60°	4.2	0.4
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1015.8	87.2
0°-40°	1140.4	97.9
0°-60°	1164.3	99.9
0°-90°	1164.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1164.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2017	
5°	1968	183
15°	1549	428
25°	920	405
35°	168	125
45°	23	20
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280657

CATALOG NUMBER: LDA2B159027D010 EU2B15WFL559027 2LBALD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2016.6
1°	2009.1
2°	1999.9
3°	1992.3
4°	1982.6
5°	1968.0
6°	1949.1
7°	1923.7
8°	1889.7
9°	1850.2
10°	1809.2
11°	1763.8
12°	1715.7
13°	1663.3
14°	1608.8
15°	1549.3
17.5°	1392.1
20°	1247.9
22.5°	1101.5
25°	920.5
27.5°	702.3
30°	481.3
32.5°	295.5
35°	168.5
37.5°	94.0
40°	54.6
42.5°	34.0
45°	22.7
47.5°	15.1
50°	9.7
52.5°	6.5
55°	4.3
57.5°	2.7
60°	1.1
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280657

CATALOG NUMBER: LDA2B159027D010 EU2B15WFL559027 2LBALD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)