

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280572

Luminaire Tested: **LDA2B158030D010 EU2B15WFL558030 2LBALD1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280572  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B158030D010 EU2B15WFL558030 2LBALD1MW  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl w/lens Self-Flanged, MW  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1523.8 lumens  
Efficiency: N/A  
Efficacy: 108.1 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280572

CATALOG NUMBER: LDA2B158030D010 EU2B15WFL558030 2LBALD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P280572

CATALOG NUMBER: LDA2B158030D010 EU2B15WFL558030 2LBALD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 99  | 98  | 97  | 97  | 95  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 98  | 95  | 97  | 95  | 93  | 95  | 93  | 91  | 90  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 91  | 95  | 92  | 89  | 93  | 90  | 88  | 91  | 88  | 86  | 85  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 84  | 89  | 85  | 83  | 87  | 84  | 82  | 80  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  | 85  | 81  | 78  | 83  | 80  | 78  | 76  |
| 6   | 92  | 84  | 79  | 75  | 91  | 84  | 79  | 75  | 82  | 78  | 75  | 81  | 77  | 74  | 80  | 76  | 74  | 72  |
| 7   | 88  | 80  | 75  | 71  | 87  | 80  | 75  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 69  |
| 8   | 85  | 76  | 71  | 68  | 84  | 76  | 71  | 67  | 75  | 70  | 67  | 74  | 70  | 67  | 73  | 69  | 67  | 65  |
| 9   | 81  | 73  | 68  | 64  | 80  | 72  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 64  | 70  | 66  | 64  | 62  |
| 10  | 78  | 70  | 65  | 61  | 77  | 69  | 64  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 63  | 61  | 59  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1301390 |
| 5°  | 1274863 |
| 10° | 1185552 |
| 15° | 1035118 |
| 20° | 856998  |
| 25° | 655469  |
| 30° | 358674  |
| 35° | 132804  |
| 40° | 45984   |
| 45° | 20722   |
| 50° | 9748    |
| 55° | 4903    |
| 60° | 1381    |
| 65° | 817     |
| 70° | 1010    |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P280572

CATALOG NUMBER: LDA2B158030D010 EU2B15WFL558030 2LBALD1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 239.2  | 15.7      |
| 10°-20°   | 560.1  | 36.8      |
| 20°-30°   | 529.4  | 34.7      |
| 30°-40°   | 163.0  | 10.7      |
| 40°-50°   | 25.8   | 1.7       |
| 50°-60°   | 5.5    | 0.4       |
| 60°-70°   | 0.8    | 0.1       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1328.7 | 87.2      |
| 0°-40°    | 1491.7 | 97.9      |
| 0°-60°    | 1523.0 | 99.9      |
| 0°-90°    | 1523.8 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1523.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2638 |      |
| 5°  | 2574 | 239  |
| 15° | 2027 | 560  |
| 25° | 1204 | 529  |
| 35° | 220  | 163  |
| 45° | 30   | 26   |
| 55° | 6    | 5    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P280572

CATALOG NUMBER: LDA2B158030D010 EU2B15WFL558030 2LBALD1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2637.8 |
| 1°    | 2627.9 |
| 2°    | 2615.9 |
| 3°    | 2606.0 |
| 4°    | 2593.3 |
| 5°    | 2574.2 |
| 6°    | 2549.5 |
| 7°    | 2516.3 |
| 8°    | 2471.7 |
| 9°    | 2420.2 |
| 10°   | 2366.5 |
| 11°   | 2307.1 |
| 12°   | 2244.2 |
| 13°   | 2175.7 |
| 14°   | 2104.3 |
| 15°   | 2026.6 |
| 17.5° | 1820.9 |
| 20°   | 1632.3 |
| 22.5° | 1440.8 |
| 25°   | 1204.1 |
| 27.5° | 918.6  |
| 30°   | 629.6  |
| 32.5° | 386.5  |
| 35°   | 220.5  |
| 37.5° | 123.0  |
| 40°   | 71.4   |
| 42.5° | 44.5   |
| 45°   | 29.7   |
| 47.5° | 19.8   |
| 50°   | 12.7   |
| 52.5° | 8.5    |
| 55°   | 5.7    |
| 57.5° | 3.5    |
| 60°   | 1.4    |
| 62.5° | 0.7    |
| 65°   | 0.7    |
| 67.5° | 0.7    |
| 70°   | 0.7    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P280572

CATALOG NUMBER: LDA2B158030D010 EU2B15WFL558030 2LBALD1MW

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)