

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498921

Luminaire Tested: **LDA2B159035R20D010 2LBD1WHH-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498921
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159035R20D010 2LBD1WHH-30DEG TILT
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 767.8 lumens
Efficiency: N/A
Efficacy: 54.5 lumens/watt
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498921

CATALOG NUMBER: LDA2B159035R20D010 2LBD1WHH-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P498921

CATALOG NUMBER: LDA2B159035R20D010 2LBD1WHH-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82					82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74					74			
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66					66			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43					43			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38					38			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	12186	12186	12186
5°	23326	10796	7874
10°	55758	9418	5310
15°	324694	7508	2094
20°	1619701	4620	630
25°	2953395	1579	0
30°	3463970	0	0
35°	3031895	0	0
40°	2238934	0	0
45°	807051	0	0
50°	168090	0	0
55°	38449	516	0
60°	12235	592	0
65°	2802	1401	0
70°	0	1731	865
75°	0	2287	0
80°	0	3409	0
85°	0	6793	0



TEST NUMBER: P498921

CATALOG NUMBER: LDA2B159035R20D010 2LBD1WHH-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.8	0.4
10°-20°	42.2	5.5
20°-30°	284.3	37.0
30°-40°	332.2	43.3
40°-50°	96.9	12.6
50°-60°	6.5	0.8
60°-70°	1.2	0.2
70°-80°	1.0	0.1
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	329.3	42.9
0°-40°	661.5	86.1
0°-60°	764.8	99.6
0°-90°	767.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	767.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	25	25	25	25	25	
5°	47	34	22	18	16	6
15°	636	72	15	8	4	332
25°	5425	111	3	0	0	2402
35°	5034	60	0	0	0	3093
45°	1157	12	0	0	0	1066
55°	45	2	1	1	0	57
65°	2	1	1	1	0	4
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P498921

CATALOG NUMBER: LDA2B159035R20D010 2LBD1WHH-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7
2.5°	31.8	31.8	28.3	25.3	23.0	21.8	21.2	20.0	19.4
5°	47.1	41.2	34.1	26.5	21.8	20.0	18.2	16.5	15.9
7.5°	68.9	60.0	41.2	27.1	20.6	17.7	15.9	14.1	12.9
10°	111.3	86.5	50.6	27.1	18.8	15.3	12.9	11.2	10.6
12.5°	205.4	132.4	60.6	26.5	17.1	12.9	10.0	8.8	7.1
15°	635.7	274.3	71.8	25.3	14.7	10.0	7.7	4.7	4.1
17.5°	1644.0	640.4	80.1	22.4	11.8	7.1	3.5	2.9	2.9
20°	3085.0	1161.4	91.8	19.4	8.8	4.7	2.4	1.8	1.2
21°	3519.4	1421.0	97.7	18.2	7.7	2.9	1.8	0.6	0.6
22°	4194.6	1704.1	102.4	17.1	6.5	1.8	1.2	0.6	0.0
23°	4675.5	1884.8	107.1	15.3	4.7	1.8	0.6	0.0	0.0
24°	5156.4	2114.9	110.1	14.1	4.1	1.2	0.6	0.0	0.0
25°	5425.4	2306.8	111.3	12.9	2.9	0.6	0.0	0.0	0.0
26°	5646.7	2435.2	111.8	11.8	1.8	0.0	0.0	0.0	0.0
27°	5836.3	2584.1	110.7	10.6	1.8	0.0	0.0	0.0	0.0
28°	5944.0	2608.8	108.9	9.4	0.6	0.0	0.0	0.0	0.0
29°	5990.5	2578.8	103.6	8.2	0.6	0.0	0.0	0.0	0.0
30°	6080.5	2550.5	98.3	7.7	0.0	0.0	0.0	0.0	0.0
31°	5997.5	2456.9	91.8	6.5	0.0	0.0	0.0	0.0	0.0
32°	5672.6	2378.1	84.2	5.3	0.0	0.0	0.0	0.0	0.0
33°	5575.5	2216.2	75.9	4.7	0.0	0.0	0.0	0.0	0.0
34°	5392.4	1975.4	68.9	4.1	0.0	0.0	0.0	0.0	0.0
35°	5034.0	1776.5	60.0	3.5	0.0	0.0	0.0	0.0	0.0
36°	4783.8	1549.3	52.4	2.9	0.0	0.0	0.0	0.0	0.0
37°	4521.9	1350.9	46.5	2.4	0.0	0.0	0.0	0.0	0.0
38°	4196.3	1142.5	39.4	1.8	0.0	0.0	0.0	0.0	0.0
39°	3817.3	944.2	33.6	1.8	0.0	0.0	0.0	0.0	0.0
40°	3476.4	761.1	28.8	1.2	0.0	0.0	0.0	0.0	0.0
42.5°	2145.6	434.4	17.1	1.2	0.0	0.0	0.0	0.0	0.0
45°	1156.7	263.7	12.4	0.6	0.0	0.0	0.0	0.0	0.0
47.5°	532.7	123.0	8.8	0.6	0.0	0.0	0.0	0.0	0.0
50°	219.0	54.7	6.5	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	78.9	30.6	4.1	0.0	0.0	0.6	0.0	0.0	0.0
55°	44.7	17.7	2.4	0.6	0.6	0.6	0.6	0.0	0.0
57.5°	21.2	10.0	0.6	0.6	0.6	0.6	0.6	0.0	0.0
60°	12.4	5.3	0.6	0.6	0.6	1.2	0.6	0.0	0.0
62.5°	5.9	1.8	0.6	1.2	1.2	1.2	1.2	0.6	0.0
65°	2.4	0.6	1.2	1.2	1.2	1.8	1.2	0.6	0.0
67.5°	0.6	0.6	1.2	1.2	1.2	1.8	1.2	0.6	0.6
70°	0.0	0.6	1.2	1.2	1.2	1.8	1.2	0.6	0.6
72.5°	0.0	0.6	1.2	1.2	1.2	1.8	1.2	0.6	0.6
75°	0.0	0.6	1.2	1.2	1.2	1.2	1.2	0.6	0.0
77.5°	0.0	0.6	1.2	1.2	1.2	1.2	1.2	0.6	0.0
80°	0.0	0.6	1.2	1.2	1.2	1.2	1.2	0.6	0.0



TEST NUMBER: P498921

CATALOG NUMBER: LDA2B159035R20D010 2LBD1WHH-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.6	1.2	1.2	1.2	1.2	1.2	0.6	0.0
85°	0.0	0.6	1.2	1.2	1.2	1.2	1.2	0.6	0.0
87.5°	0.0	0.6	1.2	1.2	1.2	1.2	0.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)