

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499049

Luminaire Tested: **LDA2B159035R45D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499049  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159035R45D010 2LBDLC1MB  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1216.6 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499049

CATALOG NUMBER: LDA2B159035R45D010 2LBDLC1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P499049

CATALOG NUMBER: LDA2B159035R45D010 2LBDLC1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1205875
5°	1179281
10°	1094124
15°	933067
20°	702483
25°	423516
30°	204175
35°	92571
40°	42571
45°	21978
50°	11590
55°	4301
60°	1283
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P499049

CATALOG NUMBER: LDA2B159035R45D010 2LBDLC1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	221.4	18.2
10°-20°	498.9	41.0
20°-30°	356.4	29.3
30°-40°	106.8	8.8
40°-50°	26.5	2.2
50°-60°	5.5	0.5
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1076.7	88.5
0°-40°	1183.5	97.3
0°-60°	1215.5	99.9
0°-90°	1216.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1216.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2444	
5°	2381	221
15°	1827	499
25°	778	356
35°	154	107
45°	32	26
55°	5	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499049

CATALOG NUMBER: LDA2B159035R45D010 2LBDLC1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2444.2
1°	2448.6
2°	2442.9
3°	2422.1
4°	2407.0
5°	2381.2
6°	2355.3
7°	2327.6
8°	2282.3
9°	2239.4
10°	2184.0
11°	2128.6
12°	2058.6
13°	1983.7
14°	1913.8
15°	1826.8
16°	1741.8
17°	1645.4
18°	1554.1
19°	1441.9
20°	1338.0
21°	1222.7
22.5°	1050.7
23°	992.8
24°	880.0
25°	778.0
26°	675.9
27°	582.7
28°	495.8
29°	424.6
30°	358.4
32.5°	235.6
35°	153.7
37.5°	100.8
40°	66.1
42.5°	44.7
45°	31.5
47.5°	22.7
50°	15.1
52.5°	9.4
55°	5.0
57.5°	2.5
60°	1.3
62.5°	1.3
65°	0.6



TEST NUMBER: P499049

CATALOG NUMBER: LDA2B159035R45D010 2LBDLC1MB

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)