

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497538

Luminaire Tested: **LDA2B158030R45D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P497538  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B158030R45D010 2LBDLC1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1452.9 lumens  
Efficiency: N/A  
Efficacy: 103.0 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P497538

CATALOG NUMBER: LDA2B158030R45D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P497538

CATALOG NUMBER: LDA2B158030R45D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1440024
5°	1408283
10°	1306587
15°	1114286
20°	838884
25°	505715
30°	243825
35°	110579
40°	50879
45°	26234
50°	13892
55°	5161
60°	1480
65°	934
70°	1154
75°	0
80°	0
85°	0



TEST NUMBER: P497538

CATALOG NUMBER: LDA2B158030R45D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	264.4	18.2
10°-20°	595.7	41.0
20°-30°	425.6	29.3
30°-40°	127.6	8.8
40°-50°	31.7	2.2
50°-60°	6.6	0.5
60°-70°	1.0	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1285.7	88.5
0°-40°	1413.3	97.3
0°-60°	1451.6	99.9
0°-90°	1452.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1452.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2919	
5°	2844	264
15°	2182	596
25°	929	426
35°	184	128
45°	38	32
55°	6	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497538

CATALOG NUMBER: LDA2B158030R45D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2918.8
1°	2924.1
2°	2917.3
3°	2892.5
4°	2874.4
5°	2843.6
6°	2812.7
7°	2779.6
8°	2725.5
9°	2674.3
10°	2608.1
11°	2541.9
12°	2458.4
13°	2368.9
14°	2285.4
15°	2181.6
16°	2080.0
17°	1964.9
18°	1855.8
19°	1721.9
20°	1597.8
21°	1460.1
22.5°	1254.8
23°	1185.6
24°	1050.9
25°	929.0
26°	807.2
27°	695.8
28°	592.0
29°	507.0
30°	428.0
32.5°	281.3
35°	183.6
37.5°	120.4
40°	79.0
42.5°	53.4
45°	37.6
47.5°	27.1
50°	18.1
52.5°	11.3
55°	6.0
57.5°	3.0
60°	1.5
62.5°	1.5
65°	0.8



TEST NUMBER: P497538

CATALOG NUMBER: LDA2B158030R45D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)