

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497557

Luminaire Tested: **LDA2B158030R60D010 2LBDL1WH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497557
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158030R60D010 2LBDL1WH
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1279.7 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497557

CATALOG NUMBER: LDA2B158030R60D010 2LBDL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P497557

CATALOG NUMBER: LDA2B158030R60D010 2LBDL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94					94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88					88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82					82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76					76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71					71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67					67			
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63					63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59					59			
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55					55			
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	54	52					52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	757409
5°	737669
10°	717343
15°	681821
20°	622942
25°	534947
30°	398039
35°	233686
40°	111354
45°	51980
50°	25866
55°	9032
60°	2072
65°	1634
70°	1010
75°	1334
80°	0
85°	0



TEST NUMBER: P497557

CATALOG NUMBER: LDA2B158030R60D010 2LBDL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.2	11.0
10°-20°	371.4	29.0
20°-30°	441.0	34.5
30°-40°	248.9	19.5
40°-50°	64.7	5.1
50°-60°	11.8	0.9
60°-70°	1.2	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	952.6	74.4
0°-40°	1201.5	93.9
0°-60°	1278.0	99.9
0°-90°	1279.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1279.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1535	
5°	1490	140
15°	1335	371
25°	983	441
35°	388	249
45°	74	65
55°	10	12
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P497557

CATALOG NUMBER: LDA2B158030R60D010 2LBDL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1535.2
1°	1535.9
2°	1525.4
3°	1516.2
4°	1498.7
5°	1489.5
6°	1473.3
7°	1461.4
8°	1450.1
9°	1442.4
10°	1431.9
11°	1411.5
12°	1392.5
13°	1382.0
14°	1357.4
15°	1334.9
16°	1308.9
17°	1277.9
18°	1248.4
19°	1213.3
20°	1186.5
21°	1150.0
22.5°	1089.5
23°	1079.0
24°	1027.7
25°	982.7
26°	932.8
27°	875.2
28°	818.2
29°	762.7
30°	698.7
32.5°	537.7
35°	388.0
37.5°	265.0
40°	172.9
42.5°	113.2
45°	74.5
47.5°	50.6
50°	33.7
52.5°	21.1
55°	10.5
57.5°	4.2
60°	2.1
62.5°	1.4
65°	1.4



TEST NUMBER: P497557

CATALOG NUMBER: LDA2B158030R60D010 2LBDL1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)