

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499065

Luminaire Tested: **LDA2B159035R60D010 2LBDL1LI**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499065  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159035R60D010 2LBDL1LI  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1071.7 lumens  
Efficiency: N/A  
Efficacy: 76.0 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499065  
CATALOG NUMBER: LDA2B159035R60D010 2LBDL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P499065

CATALOG NUMBER: LDA2B159035R60D010 2LBDL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	634266
5°	617721
10°	600666
15°	570934
20°	521664
25°	447958
30°	333323
35°	195682
40°	93257
45°	43538
50°	21721
55°	7569
60°	1776
65°	1401
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P499065

CATALOG NUMBER: LDA2B159035R60D010 2LBDL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.4	11.0
10°-20°	311.0	29.0
20°-30°	369.3	34.5
30°-40°	208.4	19.4
40°-50°	54.2	5.1
50°-60°	9.9	0.9
60°-70°	1.0	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	797.7	74.4
0°-40°	1006.1	93.9
0°-60°	1070.2	99.9
0°-90°	1071.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1071.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1286	
5°	1247	117
15°	1118	311
25°	823	369
35°	325	208
45°	62	54
55°	9	10
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P499065

CATALOG NUMBER: LDA2B159035R60D010 2LBDL1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1285.6
1°	1286.2
2°	1277.3
3°	1269.7
4°	1255.0
5°	1247.3
6°	1233.8
7°	1223.8
8°	1214.3
9°	1207.9
10°	1199.0
11°	1182.0
12°	1166.1
13°	1157.2
14°	1136.6
15°	1117.8
16°	1096.0
17°	1070.1
18°	1045.4
19°	1016.0
20°	993.6
21°	963.0
22.5°	912.4
23°	903.5
24°	860.6
25°	822.9
26°	781.1
27°	732.8
28°	685.2
29°	638.7
30°	585.1
32.5°	450.3
35°	324.9
37.5°	221.9
40°	144.8
42.5°	94.8
45°	62.4
47.5°	42.4
50°	28.3
52.5°	17.7
55°	8.8
57.5°	3.5
60°	1.8
62.5°	1.2
65°	1.2



TEST NUMBER: P499065

CATALOG NUMBER: LDA2B159035R60D010 2LBDL1LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)