

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497581

Luminaire Tested: **LDA2B158030R65D010 2LBDL1WHH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P497581  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B158030R65D010 2LBDL1WHH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1315.8 lumens  
Efficiency: N/A  
Efficacy: 93.3 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P497581

CATALOG NUMBER: LDA2B158030R65D010 2LBDL1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P497581

CATALOG NUMBER: LDA2B158030R65D010 2LBDL1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	688388
5°	659718
10°	628220
15°	597085
20°	555424
25°	512737
30°	444924
35°	319210
40°	173375
45°	74028
50°	31853
55°	11526
60°	2072
65°	1634
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P497581

CATALOG NUMBER: LDA2B158030R65D010 2LBDL1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.7	9.5
10°-20°	327.4	24.9
20°-30°	428.1	32.5
30°-40°	325.7	24.8
40°-50°	94.1	7.2
50°-60°	14.2	1.1
60°-70°	1.2	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	880.3	66.9
0°-40°	1206.0	91.7
0°-60°	1314.3	99.9
0°-90°	1315.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1315.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1395	
5°	1332	125
15°	1169	327
25°	942	428
35°	530	326
45°	106	94
55°	13	14
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497581

CATALOG NUMBER: LDA2B158030R65D010 2LBDL1WHH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1395.3
1°	1390.4
2°	1382.7
3°	1367.2
4°	1350.3
5°	1332.1
6°	1314.5
7°	1299.0
8°	1284.3
9°	1270.9
10°	1254.0
11°	1239.3
12°	1223.8
13°	1208.3
14°	1191.5
15°	1169.0
16°	1152.1
17°	1131.7
18°	1100.8
19°	1084.6
20°	1057.9
21°	1034.0
22.5°	997.5
23°	983.4
24°	961.6
25°	941.9
26°	915.9
27°	887.1
28°	855.5
29°	821.7
30°	781.0
32.5°	669.2
35°	530.0
37.5°	390.8
40°	269.2
42.5°	170.8
45°	106.1
47.5°	66.1
50°	41.5
52.5°	24.6
55°	13.4
57.5°	4.9
60°	2.1
62.5°	1.4
65°	1.4



TEST NUMBER: P497581

CATALOG NUMBER: LDA2B158030R65D010 2LBDL1WHH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)