

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499091

Luminaire Tested: **LDA2B159035R65D010 2LBDL1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499091
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159035R65D010 2LBDL1MW
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1101.8 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499091

CATALOG NUMBER: LDA2B159035R65D010 2LBDL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P499091

CATALOG NUMBER: LDA2B159035R65D010 2LBDL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	576444
5°	552447
10°	526071
15°	499989
20°	465119
25°	429395
30°	372574
35°	267293
40°	145166
45°	62027
50°	26633
55°	9634
60°	1776
65°	1401
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P499091

CATALOG NUMBER: LDA2B159035R65D010 2LBDL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	9.5
10°-20°	274.2	24.9
20°-30°	358.5	32.5
30°-40°	272.7	24.8
40°-50°	78.8	7.2
50°-60°	11.9	1.1
60°-70°	1.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.1	66.9
0°-40°	1009.9	91.7
0°-60°	1100.6	99.9
0°-90°	1101.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1101.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1168	
5°	1116	104
15°	979	274
25°	789	359
35°	444	273
45°	89	79
55°	11	12
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499091

CATALOG NUMBER: LDA2B159035R65D010 2LBDL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1168.4
1°	1164.3
2°	1157.8
3°	1144.9
4°	1130.8
5°	1115.5
6°	1100.7
7°	1087.8
8°	1075.4
9°	1064.2
10°	1050.1
11°	1037.8
12°	1024.8
13°	1011.9
14°	997.7
15°	978.9
16°	964.8
17°	947.7
18°	921.8
19°	908.3
20°	885.9
21°	865.9
22.5°	835.3
23°	823.5
24°	805.2
25°	788.8
26°	767.0
27°	742.9
28°	716.4
29°	688.1
30°	654.0
32.5°	560.4
35°	443.8
37.5°	327.3
40°	225.4
42.5°	143.0
45°	88.9
47.5°	55.3
50°	34.7
52.5°	20.6
55°	11.2
57.5°	4.1
60°	1.8
62.5°	1.2
65°	1.2



TEST NUMBER: P499091

CATALOG NUMBER: LDA2B159035R65D010 2LBDL1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)