

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315078

Luminaire Tested: **LDA2B15NFL9027D010 PINW1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B15NFL9027D010 PINW1MMS
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in Adj PinHole, White oculus, matte metallic silver finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1020.7 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315078

CATALOG NUMBER: LDA2B15NFL9027D010 PINW1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P315078

CATALOG NUMBER: LDA2B15NFL9027D010 PINW1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	99	97	97	97	97	97	97	97	97															
	1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	99	99	99	99	99	99	99	99	99	99	99	97															
	2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	96	96	96	96	96	96	96	96	96	96	96	94															
	3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	93	93	93	93	93	93	93	93	93	93	93	91															
	4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	90	90	90	90	90	90	90	90	90	90	90	89															
	5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86	86	86	86	86	86	86	86															
	6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84	84	84	84	84	84	84	84															
	7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82	82	82	82	82	82	82	82															
	8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80	80	80	80	80	80	80	80															
	9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78	78	78	78	78	78															
	10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76	76	76	76	76	76	76	76	76															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2612548
5°	2409423
10°	1623652
15°	800523
20°	341949
25°	134404
30°	52924
35°	23188
40°	11142
45°	5372
50°	2993
55°	1634
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P315078

CATALOG NUMBER: LDA2B15NFL9027D010 PINW1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	412.1	40.4
10°-20°	443.8	43.5
20°-30°	128.2	12.6
30°-40°	27.0	2.6
40°-50°	6.6	0.7
50°-60°	1.9	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	984.1	96.4
0°-40°	1011.1	99.1
0°-60°	1019.7	99.9
0°-90°	1020.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1020.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5295	
5°	4865	412
15°	1567	444
25°	247	128
35°	38	27
45°	8	7
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315078

CATALOG NUMBER: LDA2B15NFL9027D010 PINW1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	5295.4
1°	5262.2
2°	5205.9
3°	5129.8
4°	5022.0
5°	4865.1
6°	4653.3
7°	4377.0
8°	4037.2
9°	3641.0
10°	3241.0
11°	2836.6
12°	2454.9
13°	2116.1
14°	1818.1
15°	1567.3
17.5°	1035.9
20°	651.3
22.5°	400.5
25°	246.9
27.5°	150.7
30°	92.9
32.5°	58.7
35°	38.5
37.5°	25.5
40°	17.3
42.5°	12.0
45°	7.7
47.5°	4.8
50°	3.9
52.5°	2.9
55°	1.9
57.5°	1.4
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P315078

CATALOG NUMBER: LDA2B15NFL9027D010 PINW1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)