

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497589

Luminaire Tested: **LDA2B158030R70D010 2LBD1LI**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497589
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158030R70D010 2LBD1LI
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1378.4 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497589
CATALOG NUMBER: LDA2B158030R70D010 2LBD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P497589

CATALOG NUMBER: LDA2B158030R70D010 2LBD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50		59	54	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	538603
5°	532637
10°	529979
15°	528132
20°	509274
25°	488241
30°	483321
35°	412805
40°	257615
45°	119170
50°	43135
55°	3011
60°	1381
65°	1634
70°	1010
75°	1334
80°	0
85°	0



TEST NUMBER: P497589

CATALOG NUMBER: LDA2B158030R70D010 2LBD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	7.4
10°-20°	289.6	21.0
20°-30°	416.4	30.2
30°-40°	410.5	29.8
40°-50°	146.3	10.6
50°-60°	12.0	0.9
60°-70°	1.1	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.0	58.6
0°-40°	1218.5	88.4
0°-60°	1376.8	99.9
0°-90°	1378.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1378.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1092	
5°	1076	102
15°	1034	290
25°	897	416
35°	685	410
45°	171	146
55°	4	12
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P497589

CATALOG NUMBER: LDA2B158030R70D010 2LBD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1091.7
1°	1091.7
2°	1089.5
3°	1090.2
4°	1081.1
5°	1075.5
6°	1067.8
7°	1064.9
8°	1061.4
9°	1060.7
10°	1057.9
11°	1054.4
12°	1054.4
13°	1048.1
14°	1039.6
15°	1034.0
16°	1022.8
17°	1016.4
18°	996.8
19°	983.4
20°	970.0
21°	952.5
22.5°	927.9
23°	918.0
24°	908.9
25°	896.9
26°	889.9
27°	878.0
28°	876.6
29°	863.9
30°	848.4
32.5°	788.7
35°	685.4
37.5°	551.1
40°	400.0
42.5°	273.4
45°	170.8
47.5°	101.9
50°	56.2
52.5°	21.1
55°	3.5
57.5°	2.1
60°	1.4
62.5°	1.4
65°	1.4



TEST NUMBER: P497589

CATALOG NUMBER: LDA2B158030R70D010 2LBD1LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)