

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279766

Luminaire Tested: **LDA2B159030D010 EU2B15FL409030 2LBAD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159030D010 EU2B15FL409030 2LBAD1WMH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1248.3 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279766

CATALOG NUMBER: LDA2B159030D010 EU2B15FL409030 2LBAD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P279766

CATALOG NUMBER: LDA2B159030D010 EU2B15FL409030 2LBAD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																			
	2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																			
	3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																																			
	4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																																			
	5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																																			
	6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																																			
	7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																																			
	8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																			
	9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																																			
	10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1716455
5°	1680173
10°	1531323
15°	1196264
20°	708258
25°	263309
30°	82263
35°	36559
40°	17003
45°	8024
50°	4375
55°	2494
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P279766

CATALOG NUMBER: LDA2B159030D010 EU2B15FL409030 2LBAD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	313.6	25.1
10°-20°	623.6	50.0
20°-30°	255.4	20.5
30°-40°	42.3	3.4
40°-50°	10.0	0.8
50°-60°	2.7	0.2
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1192.6	95.5
0°-40°	1234.9	98.9
0°-60°	1247.6	99.9
0°-90°	1248.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1248.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3479	
5°	3393	314
15°	2342	624
25°	484	255
35°	61	42
45°	12	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279766

CATALOG NUMBER: LDA2B159030D010 EU2B15FL409030 2LBAD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3479.1
1°	3467.1
2°	3451.0
3°	3436.7
4°	3417.8
5°	3392.6
6°	3355.3
7°	3306.6
8°	3237.3
9°	3153.0
10°	3056.7
11°	2945.0
12°	2818.9
13°	2675.1
14°	2515.2
15°	2342.1
17.5°	1857.3
20°	1349.0
22.5°	863.6
25°	483.7
27.5°	255.0
30°	144.4
32.5°	91.7
35°	60.7
37.5°	40.1
40°	26.4
42.5°	17.2
45°	11.5
47.5°	8.0
50°	5.7
52.5°	4.0
55°	2.9
57.5°	1.7
60°	1.1
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279766

CATALOG NUMBER: LDA2B159030D010 EU2B15FL409030 2LBAD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)