

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497605

Luminaire Tested: **LDA2B158030R70D010 2LBDL1WMH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158030R70D010 2LBDL1WMH
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1276.3 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497605

CATALOG NUMBER: LDA2B158030R70D010 2LBDL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P497605

CATALOG NUMBER: LDA2B158030R70D010 2LBDL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	505301
5°	502328
10°	499019
15°	489722
20°	472050
25°	451931
30°	430511
35°	355227
40°	230888
45°	120636
50°	56107
55°	20558
60°	2072
65°	1634
70°	1010
75°	1334
80°	0
85°	0



TEST NUMBER: P497605

CATALOG NUMBER: LDA2B158030R70D010 2LBDL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.9	7.5
10°-20°	269.4	21.1
20°-30°	382.4	30.0
30°-40°	357.6	28.0
40°-50°	143.8	11.3
50°-60°	25.1	2.0
60°-70°	1.2	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	747.8	58.6
0°-40°	1105.4	86.6
0°-60°	1274.4	99.9
0°-90°	1276.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1276.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1024	
5°	1014	96
15°	959	269
25°	830	382
35°	590	358
45°	173	144
55°	24	25
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P497605

CATALOG NUMBER: LDA2B158030R70D010 2LBDL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1024.2
1°	1025.6
2°	1023.5
3°	1019.3
4°	1017.1
5°	1014.3
6°	1003.1
7°	1006.6
8°	996.8
9°	994.7
10°	996.1
11°	986.9
12°	984.8
13°	973.6
14°	969.3
15°	958.8
16°	952.5
17°	939.8
18°	925.1
19°	916.6
20°	899.1
21°	885.7
22.5°	861.1
23°	854.8
24°	842.8
25°	830.2
26°	820.3
27°	806.3
28°	792.2
29°	775.3
30°	755.7
32.5°	686.8
35°	589.8
37.5°	475.2
40°	358.5
42.5°	255.9
45°	172.9
47.5°	113.9
50°	73.1
52.5°	45.7
55°	23.9
57.5°	7.7
60°	2.1
62.5°	1.4
65°	1.4



TEST NUMBER: P497605

CATALOG NUMBER: LDA2B158030R70D010 2LBDL1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)