

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497607

Luminaire Tested: **LDA2B158030R70D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497607
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158030R70D010 2LBDLC1MMS
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1378.5 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497607

CATALOG NUMBER: LDA2B158030R70D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P497607

CATALOG NUMBER: LDA2B158030R70D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	545707
5°	542542
10°	538946
15°	528898
20°	509799
25°	488077
30°	464920
35°	383655
40°	249372
45°	130334
50°	60635
55°	22192
60°	2269
65°	1751
70°	1154
75°	1525
80°	0
85°	0



TEST NUMBER: P497607

CATALOG NUMBER: LDA2B158030R70D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	7.5
10°-20°	291.0	21.1
20°-30°	413.0	30.0
30°-40°	386.2	28.0
40°-50°	155.3	11.3
50°-60°	27.2	2.0
60°-70°	1.3	0.1
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	807.7	58.6
0°-40°	1193.9	86.6
0°-60°	1376.4	99.9
0°-90°	1378.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1378.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1106	
5°	1096	104
15°	1036	291
25°	897	413
35°	637	386
45°	187	155
55°	26	27
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P497607

CATALOG NUMBER: LDA2B158030R70D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1106.1
1°	1107.7
2°	1105.4
3°	1100.8
4°	1098.5
5°	1095.5
6°	1083.4
7°	1087.2
8°	1076.5
9°	1074.3
10°	1075.8
11°	1065.9
12°	1063.6
13°	1051.5
14°	1046.9
15°	1035.5
16°	1028.7
17°	1015.0
18°	999.1
19°	990.0
20°	971.0
21°	956.6
22.5°	930.0
23°	923.2
24°	910.3
25°	896.6
26°	886.0
27°	870.8
28°	855.6
29°	837.4
30°	816.1
32.5°	741.7
35°	637.0
37.5°	513.2
40°	387.2
42.5°	276.3
45°	186.8
47.5°	123.0
50°	79.0
52.5°	49.3
55°	25.8
57.5°	8.4
60°	2.3
62.5°	1.5
65°	1.5



TEST NUMBER: P497607

CATALOG NUMBER: LDA2B158030R70D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)