

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278868

Luminaire Tested: **LDA2B159030D010 EU2B15NFL259030 2LBAD1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278868  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B159030D010 EU2B15NFL259030 2LBAD1MW  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl, Self-Flanged, MW  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1216.2 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278868

CATALOG NUMBER: LDA2B159030D010 EU2B15NFL259030 2LBAD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P278868

CATALOG NUMBER: LDA2B159030D010 EU2B15NFL259030 2LBAD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97	97	97	97	97	97	97	97																
	2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94	94	94	94	94	94	94	94																
	3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91	91	91	91	91	91	91	91																
	4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89	89	89	89	89	89	89																
	5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86	86	86	86	86	86	86																
	6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84	84	84	84	84	84	84																
	7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82	82	82	82	82	82	82																
	8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80	80	80	80	80	80	80																
	9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78	78	78	78	78																
	10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76	76	76	76	76	76	76	76																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3113064
5°	2871042
10°	1934706
15°	953906
20°	407472
25°	160152
30°	63064
35°	27645
40°	13267
45°	6419
50°	3531
55°	1978
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P278868

CATALOG NUMBER: LDA2B159030D010 EU2B15NFL259030 2LBAD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	491.1	40.4
10°-20°	528.9	43.5
20°-30°	152.7	12.6
30°-40°	32.2	2.7
40°-50°	7.9	0.7
50°-60°	2.3	0.2
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1172.6	96.4
0°-40°	1204.8	99.1
0°-60°	1215.0	99.9
0°-90°	1216.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1216.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6310	
5°	5797	491
15°	1868	529
25°	294	153
35°	46	32
45°	9	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278868

CATALOG NUMBER: LDA2B159030D010 EU2B15NFL259030 2LBAD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6309.9
1°	6270.4
2°	6203.2
3°	6112.6
4°	5984.1
5°	5797.2
6°	5544.8
7°	5215.5
8°	4810.6
9°	4338.5
10°	3861.9
11°	3380.1
12°	2925.2
13°	2521.4
14°	2166.4
15°	1867.6
17.5°	1234.3
20°	776.1
22.5°	477.2
25°	294.2
27.5°	179.5
30°	110.7
32.5°	70.0
35°	45.9
37.5°	30.4
40°	20.6
42.5°	14.3
45°	9.2
47.5°	5.7
50°	4.6
52.5°	3.4
55°	2.3
57.5°	1.7
60°	1.1
62.5°	1.1
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.6
80°	0.0
82.5°	0.0



TEST NUMBER: P278868

CATALOG NUMBER: LDA2B159030D010 EU2B15NFL259030 2LBAD1MW

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)